

KEMET Part Number: C0603C274K4RACTU
(C0603C274K4RAC7867)

Ceramic, Commercial-(CxxxxC), 0.27 uF, 10%, 16 V, 0603, X7R, SMD, MLCC, Temperature Stable, Class II



Dimensions

| Dimension | Value |
|-----------|------------------|
| L | 1.6mm +/-0.15mm |
| W | 0.8mm +/-0.15mm |
| T | 0.8mm +/-0.07mm |
| S | 0.7mm MIN |
| B | 0.35mm +/-0.15mm |

Packaging Specifications

| | |
|----------------------------|------------------------|
| Packaging: | T&R, 180mm, Paper Tape |
| Packaging Quantity: | 4000 |

General Information

| | |
|-----------------------|--|
| Style: | SMD Chip |
| Series: | Commercial-(CxxxxC) |
| Chip Size: | 0603 |
| Description: | SMD, MLCC, Temperature Stable, Class II |
| Features: | Temperature Stable, Class II |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Failure Rate: | N/A |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 1000 hours |

Specifications

| | |
|---|---------------------|
| Capacitance: | 0.27 uF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 16 VDC |
| Dielectric Withstanding Voltage: | 40 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | X7R |
| Dissipation Factor: | 3.5% |
| Aging Rate: | 3% Loss/Decade Hour |
| Insulation Resistance: | 1.852 GOhms |