

KEMET Part Number: T491C337K004AT
(B45196H0337K309)

Tantalum, MnO₂ Tantalum, T491, 330 uF, 10%, 4 V, 6032, SMD, MnO₂, Molded, 900 mOhms, Height Max = 2.8mm



Dimensions

Footprint		6032
L		6mm +/-0.3mm
W		3.2mm +/-0.3mm
H		2.5mm +/-0.3mm
T		0.13mm REF
S		1.3mm +/-0.3mm
F		2.2mm +/-0.1mm
A		2.9mm MIN
B		0.5mm +/-0.15mm
E		2.4mm REF
G		2.8mm REF
P		0.9mm REF
R		1mm REF
X		0.1mm +/-0.1mm

Packaging Specifications

Weight:	224.48 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500

General Information

Dielectric:	MnO ₂ Tantalum
Style:	SMD Chip
Series:	T491
Description:	SMD, MnO ₂ , Molded
RoHS:	Yes
Termination:	Tin

Specifications

Capacitance:	330 uF
Capacitance Tolerance:	10%
Voltage DC:	4 VDC (85C), 2.68 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	10% 120Hz 20C
Failure Rate:	N/A
Resistance:	0.9 Ohms (100kHz)
Current:	350 mAmps (100kHz 25C), 315 mAmps (85C), 140 mAmps (125C)
Leakage Current:	13.2 uAmps (5min 20C)