

KEMET Part Number: C1206C472KDRACTU
(C1206C472KDRAC7800)

Ceramic, Commercial-(CxxxxC), 4700 pF, 10%, 1,000 V, 1206, X7R, SMD, MLCC, High Voltage, Temperature Stable



Dimensions

| | |
|----------|-----------------|
| L | 3.2mm +/-0.2mm |
| W | 1.6mm +/-0.2mm |
| T | 1mm +/-0.10mm |
| B | 0.5mm +/-0.25mm |

Packaging Specifications

| | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 2500 |

General Information

| | |
|-----------------------|--|
| Style: | SMD Chip |
| Series: | Commercial-(CxxxxC) |
| Chip Size: | 1206 |
| Description: | SMD, MLCC, High Voltage, Temperature Stable |
| Features: | High Voltage |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Failure Rate: | N/A |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 1000 hours |

Specifications

| | |
|---|---------------------|
| Capacitance: | 4700 pF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 1000 VDC |
| Dielectric Withstanding Voltage: | 1,200 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | X7R |
| Dissipation Factor: | 2.5% |
| Aging Rate: | 3% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |