

KEMET Part Number: C0402H560F3GACTU
(C0402H560F3GAC7867)

Ceramic, 200C, 200C-(CxxxxH), 56 pF, 1%, 25 V, 0402, C0G, SMD, MLCC, High Temperature, Ultra-Stable, Low Loss



General Information	
Style:	SMD Chip
Series:	200C-(CxxxxH)
Chip Size:	0402
Description:	SMD, MLCC, High Temperature, Ultra-Stable, Low Loss
Features:	High Temp, Ultra-Stable, Low Loss
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A

Dimensions	
L	1mm +/-0.05mm
W	0.5mm +/-0.05mm
T	0.5mm +/-0.05mm
S	0.3mm MIN
B	0.3mm +/-0.1mm

Packaging Specifications	
Packaging:	T&R, 180mm, Paper Tape
Packaging Quantity:	10000

Specifications	
Capacitance:	56 pF
Capacitance Tolerance:	1%
Voltage DC:	25 VDC
Dielectric Withstanding Voltage:	62.5 V
Temperature Range:	-55/+200C
Temperature Coefficient:	C0G
Dissipation Factor:	0.1%
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	100 GOhms