


Tantalum, Polymer Tantalum, COTS, M550, 370 uF, 20%, 75 V, 40 mOhms



| General Information | |
|---------------------|---|
| Dielectric: | Polymer Tantalum |
| Style: | Radial Assemblies |
| Series: | M550 |
| RoHS: | No |
| Termination: | Silver |
| Lead: | 2 Tabs |
| Notes: | H1: 4.5 +/-0.1, W1: 3.2 +/-0.1. H2: 8.2 +/-0.1, W2: 4.4 +/-0.1. d: 3.2 Ref. |

| Dimensions | |
|------------|------------------|
| L | 48.4mm +/-0.38mm |
| W | 28.2mm +/-0.38mm |
| H | 11.1mm +/-0.2mm |
| S | 11.5mm REF |
| LL | 3.2mm +/-0.1mm |
| F | 0.81mm REF |

| Specifications | |
|-------------------------------|-------------------------------|
| Capacitance: | 370 uF |
| Capacitance Tolerance: | 20% |
| Voltage DC: | 75 VDC (85C), 58.5 VDC (105C) |
| Temperature Range: | -55/+105C |
| Dissipation Factor: | 5% (120Hz 25C) |
| Resistance: | 40 mOhm (100kHz 25C) |
| Current: | 7900 mAmps (40kHz 85C) |
| Leakage Current: | 208 uAmps (5min 25C) |

| Packaging Specifications | |
|----------------------------|------------|
| Weight: | 3.63 g |
| Packaging: | Bulk, Tray |
| Packaging Quantity: | 20 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.