


Aluminum Electrolytic, 85C, PEH200, 4700 uF, 20%, 63 V, -40/+85C



Dimensions

D	36.6mm +/-1mm
L	51.5mm +/-1mm
T	4.4mm NOM
S	13mm +/-0.5mm
F	8mm +/-0.5mm
DT	8mm NOM
LT	58.9mm +/-1mm

Packaging Specifications

Weight:	70 g
Sleeving:	Yes
Packaging:	Bulk
Packaging Quantity:	42

General Information

Dielectric:	Aluminum Electrolytic
Series:	PEH200
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Sleeving. M5

Specifications

Capacitance:	4700 uF
Capacitance Tolerance:	20%
Voltage DC:	63 VDC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	10000 Hrs (Rated Voltage And Ripple Current At 85C)
Resistance:	32 mOhms (100Hz 20C), 21 mOhms (100kHz 20C)
Current:	9 Amps (100Hz 85C), 26.8 Amps (10kHz 50C), 18 Amps (10kHz 40C)
Leakage Current:	4888.3 uAmps (5min 20C)
Inductance:	12 nH (ESL)