


Tantalum, MnO2 Tantalum, COTS, T497_COTS, 4.7 uF, 10%, 50 V, 7238, SMD, MnO2, Molded, COTS, Medical, B (0.1%/1000 Hrs), 1.5 Ohms, Height Max = 3.17mm



General Information	
Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Series:	T497_COTS
Description:	SMD, MnO2, Molded, COTS, Medical
Features:	COTS, Medical
RoHS:	No
Termination:	Solder Coated
Notes:	P and R dimensions represents the minimum solderable area of the termination surface entirely below cutout (if one is present).

Dimensions	
Footprint	7238
L	7.24mm +/-0.38mm
W	3.81mm +/-0.38mm
H	2.79mm +/-0.38mm
S	1.27mm +0.025/-0.13mm
F	3.68mm +0.13/-0.51mm
A	4.7mm NOM
K	1.52mm MIN
P	0.76mm MIN

Specifications	
Capacitance:	4.7 uF
Capacitance Tolerance:	10%
Voltage DC:	50 VDC (85C), 33.5 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	6%
Failure Rate:	B (0.1%/1000 Hrs)
Resistance:	1.5 Ohms (100kHz 20C)
Leakage Current:	2.4 uAmps (20C)
Testing and Reliability:	Standard Testing Only

Packaging Specifications	
Weight:	349.01 mg
Packaging:	T&R, 178mm
Packaging Quantity:	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.