


KEMET Part Number: PHE450KB6220JR17
(F450BV224J400A)

Film, Double Metallized Polypropylene, Commercial Grade, PHE450/F450, 0.22 uF, 5%, 400 V, 85C, Lead Spacing = 15mm



General Information	
Dielectric:	Double Metallized Polypropylene
Style:	Radial
Series:	PHE450/F450
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	The Rated Voltage Decreases 1.3%/C Between +85C And +105C. Rthha= 60 C/W (85C), 0.2 m/s

Dimensions	
L	18mm MAX
H	17.5mm MAX
T	9.5mm MAX
S	15mm +/-0.4mm
LL	17mm -1mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Specifications	
Capacitance:	0.22 uF
Capacitance Tolerance:	5%
Voltage DC:	400 VDC (85C), 296 VDC (105C)
Voltage AC:	250 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.03% 1kHz, 0.06% 10kHz
Insulation Resistance:	136.364 GOhms
Max dVdt:	1,000 V
Inductance:	6 nH

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	300