


KEMET Part Number: PHE450MR7220JR06L2
(F450RM225J630Z)

Film, Double Metallized Polypropylene, Commercial Grade, PHE450/F450, 2.2 uF, 5%, 630 V, 85C, Lead Spacing = 37.5mm



General Information	
Dielectric:	Double Metallized Polypropylene
Style:	Radial
Series:	PHE450/F450
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	The Rated Voltage Decreases 1.3%/C Between +85C And +105C. Rthha= 20 C/W (85C), 0.2 m/s

Dimensions	
L	41mm MAX
H	36mm MAX
T	19mm MAX
S	37.5mm +/-0.4mm
LL	18.5mm +0.5mm
F	1mm +/-0.05mm
G	0.5mm NOM

Specifications	
Capacitance:	2.2 uF
Capacitance Tolerance:	5%
Voltage DC:	630 VDC (85C), 466.2 VDC (105C)
Voltage AC:	400 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.03% 1kHz
Insulation Resistance:	13.636 GOhms
Max dVdt:	700 V
Inductance:	6 nH

Packaging Specifications	
Packaging:	Pizza
Packaging Quantity:	91