

KEMET Part Number: PME271E522MR30
(P277QN223M300A)

Film, Metallized Paper, Safety, PME271E/P277, 0.022 uF, 20%, 630 V, 300 V, 110C, Lead Spacing = 15.2mm



General Information

Dielectric:	Metallized Paper
Style:	Radial
Series:	PME271E/P277
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	ENEC, UL, cUL
Construction:	Molded
Miscellaneous:	SRF= 9.8 MHz

Dimensions

L	19mm MAX
H	13mm MAX
T	7.3mm MAX
S	15.2mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Specifications

Capacitance:	0.022 uF
Capacitance Tolerance:	20%
Voltage DC:	630 VDC
Voltage AC:	300 VAC
Temperature Range:	-40/+110C
Rated Temperature:	110C
Dissipation Factor:	1.3% 1kHz
Insulation Resistance:	12 GOhms
Max dVdt:	1,200 V
Safety Class:	X1

Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	400