


Film, Metallized Polyester, Commercial Grade, R60, 100 uF, 10%, 100 V, 85C, Lead Spacing = 37.5mm



General Information	
Dielectric:	Metallized Polyester
Style:	Radial
Series:	R60
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	Upper Operating Temperature Of 125C Is Allowed For A Maximum Operating Time Of 1,000 Hours. Above 85C, DC And AC Voltage Derating Is 1.25%/C.

Dimensions	
L	41.5mm +0.3mm
H	40mm +1mm
T	20mm +0.3mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.05mm

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	84

Specifications	
Capacitance:	100 uF
Capacitance Tolerance:	10%
Voltage DC:	100 VDC
Voltage AC:	63 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	1% 1kHz
Insulation Resistance:	12.5 MOhms
Max dVdt:	1 V
Inductance:	22 nH