

Film, Film/Foil Polypropylene, Commercial Grade, R73, 0.033 uF, 5%, 1,000 V, 85C, Lead Spacing = 22.5mm



General Information	
Dielectric:	Film/Foil Polypropylene
Style:	Radial
Series:	R73
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	AEC-Q200
AEC-Q200:	Yes
Miscellaneous:	Above 85C DC And AC Voltage Derating Is 1.25%/C

Dimensions	
L	26.5mm +0.3mm
H	16mm +0.1mm
T	7mm +0.2mm
S	22.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Specifications	
Capacitance:	0.033 uF
Capacitance Tolerance:	5%
Voltage DC:	1000 VDC
Voltage AC:	400 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.03% 1kHz, 0.04% 10kHz, 0.1% 100kHz
Insulation Resistance:	100 GOhms
Max dVdt:	11,000 V
Inductance:	18 nH

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	500