


Varistors, VC, Low Voltage, 31 V, 25 VAC, 39 V, 65 V, 1 A, 200 A, 1 J, 8000 uW



General Information	
Type:	Varistors
Style:	SMD Chip
Series:	VC
Description:	Surface Mount Varistors
Features:	Low Voltage
Termination:	Nickel Tin
RoHS:	Yes
Approvals:	CECC, IEC, AEC-Q200

Dimensions	
Chip Size	1206
L	3.2mm +/-0.3mm
W	1.6mm +/-0.2mm
T	1.25mm MAX
B	0.5mm +/-0.25mm

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	2500

Specifications	
Voltage DC:	31 VDC (25C)
Voltage AC:	25 VAC
Temperature Range:	-55/+125C
Storage Temperature Range:	-55/+150C
Varistor Voltage:	39 VDC at 1 mAmps
Clamping Voltage:	65 V
Clamping Current:	1 Amps (8/20 us MAX)
Surge Current:	200 Amps (8/20 us MAX)
Energy:	1 J (10/1000 us MAX)
Capacitance:	510 pF (1kHz)