

**KEMET Part Number: SMC10.2334J50A31TR16**  
(F125WP334J050V)

Film, Metallized PPS, Commercial Grade, SMC/F125, 0.33 uF, 5%, 50 V, 30 V, 100C, 4036, 5.5mm



Note: '()' correspond to the letters used in the product bulletin

Dimensions	
Chip Size	4036
L	10.2mm +/-0.2mm
W	9.1mm +/-0.2mm
T	5.5mm +/-0.2mm
F	0.5mm NOM

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	800

General Information	
Dielectric:	Metallized PPS
Style:	SMD Chip
Series:	SMC/F125
Features:	High Stability
RoHS:	Yes
Approvals:	AEC-Q200
AEC-Q200:	Yes

Specifications	
Capacitance:	0.33 uF
Capacitance Tolerance:	5%
Voltage DC:	50 VDC
Voltage AC:	30 V
Temperature Range:	-55/+125C
Rated Temperature:	100C
Dissipation Factor:	0.15% 1kHz, 0.25% 10kHz, 0.6% 100kHz
Insulation Resistance:	15 GOhms
Max dVdt:	4 V