



Description

The product is a single-phase DC output printed board mounted solid state relay. Control voltage is 4-32VDC, output current is 20A, 40A, or 100A @ 100VDC. The photoelectric isolation between input and output, dielectric strength $\geq 2500\text{VACrms}$.

Features

- MOSFET output
- Low on impedance
- 4-32VDC control input
- Dielectric strength $\geq 2500\text{VACrms}$
- Opto-isolation
- LED indication

Applications

Suitable for DC heating, DC power, DC valve, DC motor, Solar Energy, Medical equipment and so on.

Technical Specification

Input Circuit

Control Voltage Range	: 4V DC to 32V DC
Min. Turn-On Voltage	: 4V DC
Min. Turn-Off Voltage	: 1V DC
Max. Input Current	: 28mA @ 32V DC
Max. Reverse Voltage	: 32V DC

Output Circuit

Line Voltage Range	: 0 ~ 100V AC
Load Current Range	
20A	: 0.001 - 20A
40A	: 0.001 - 40A
100A	: 0.001 - 100A
Maximum Surge Current [@10ms] (100V DC)	
20A	: 60A
40A	: 120A
100A	: 250A
Max. Turn-on Time	: 100 μ s
Max. Turn-off Time	: 100 μ s
Max. Off-State Leakage Current [@ Rated Voltage]	: 0.1mA
Max. On-state Resistance (100V DC)	
20A, 40A	: 13m Ω max. (@TA=25°C)
100A	: 6.5m Ω max. (@TA=25°C)


Solid State Relay



General Information


Dielectric Strength (50/60Hz)	
Input/Output	: $\geq 2500V_{rms}$
Input, Output/Base	: $\geq 2500V_{rms}$
Ambient Operating Temperature Range	: $-30^{\circ}C$ to $+80^{\circ}C$
Ambient Storage Temperature Range	: $-30^{\circ}C$ to $+100^{\circ}C$
Weight (Typical) (Quick Connection Terminal)	: 90g

Diagram



Dimensions : Millimetres

Thermal Curve



Part Number Table

Description	Part Number
SSR, 20A, 100V DC	MCKSJ100D20-L
SSR, 40A, 100V DC	MCKSJ100D40-L
SSR, 100A, 4-32V DC, 0-100V DC	MCKSJ100D100-L

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
 www.farnell.com
 www.newark.com

