

**KEMET Part Number: T491D337K010AT**  
(B45196H2337K409)

Tantalum, MnO<sub>2</sub> Tantalum, T491, 330 uF, 10%, 10 V, 7343, SMD, MnO<sub>2</sub>, Molded, 500 mOhms, Height Max = 3.1mm



**Dimensions**

Footprint		7343
<b>L</b>		7.3mm +/-0.3mm
<b>W</b>		4.3mm +/-0.3mm
<b>H</b>		2.8mm +/-0.3mm
<b>T</b>		0.13mm REF
<b>S</b>		1.3mm +/-0.3mm
<b>F</b>		2.4mm +/-0.1mm
<b>A</b>		3.6mm MIN
<b>B</b>		0.5mm +/-0.15mm
<b>E</b>		3.5mm REF
<b>G</b>		3.5mm REF
<b>P</b>		0.9mm REF
<b>R</b>		1mm REF
<b>X</b>		0.1mm +/-0.1mm

**Packaging Specifications**

<b>Weight:</b>	446.84 mg
<b>Packaging:</b>	T&R, 178mm
<b>Packaging Quantity:</b>	500

**General Information**

<b>Dielectric:</b>	MnO <sub>2</sub> Tantalum
<b>Style:</b>	SMD Chip
<b>Series:</b>	T491
<b>Description:</b>	SMD, MnO <sub>2</sub> , Molded
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin

**Specifications**

<b>Capacitance:</b>	330 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	10 VDC (85C), 6.7 VDC (125C)
<b>Temperature Range:</b>	-55/+125C
<b>Dissipation Factor:</b>	10% 120Hz 20C
<b>Failure Rate:</b>	N/A
<b>Resistance:</b>	0.5 Ohms (100kHz)
<b>Current:</b>	548 mAmps (100kHz 25C), 493.2 mAmps (85C), 219.2 mAmps (125C)
<b>Leakage Current:</b>	33 uAmps (5min 20C)