

**Productname :** SERVISOL IPA 170  
**Ref.Nr.:** UDS000050\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000050\_20150304

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**SERVISOL IPA 170**  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Precision

### 1.3. Details of the supplier of the safety data sheet

**CRC Industries UK Ltd.**  
Ambersil House - Wylds Road  
Castlefield Industrial Estate  
TA6 4DD Bridgwater Somerset  
United Kingdom  
Tel.: +44 1278 727200  
Fax.: +44 1278 425644  
E-mail : hse.uk@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66

### 1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No 1272/2008

**Physical:** Aerosols, category 1  
Extremely flammable aerosol.  
Pressurised container: May burst if heated.

Classification is based on test data.

**Health:** Eye irritation, category 2  
Causes serious eye irritation.  
Specific target organ toxicity - single exposure, category 3  
May cause drowsiness or dizziness.

Classification based on calculation method.

**Environment:** Not classified





**Productname :** SERVISOL IPA 170  
**Ref.Nr.:** UDS000050\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000050\_20150304

Classification based on calculation method.

## 2.2. Label elements

### Labelling according to Regulation (EC) No 1272/2008

<b>Product identifier:</b>	Contains: propan-2-ol; isopropyl alcohol ;isopropanol
<b>Hazard pictogram(s):</b>	 
<b>Signal word:</b>	Danger
<b>Hazard statement(s):</b>	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H319 : Causes serious eye irritation. H336 : May cause drowsiness or dizziness.
<b>Precautionary statement(s):</b>	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P261 : Avoid breathing dust/fume/gas/mist/vapours/spray. P271 : Use only outdoors or in a well-ventilated area. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.

## 2.3. Other hazards

No information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
propan-2-ol; isopropyl alcohol ;isopropanol	01-2119457558-25	67-63-0	200-661-7	60-100	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B
carbon dioxide	-	124-38-9	204-696-9	1-5	Press. Gas	H280	A,G
<b>Explanation notes</b>							
A : substance with Community workplace exposure limit							
B : substance with national established workplace exposure limit							
G : exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006							



**Productname :** SERVISOL IPA 170  
**Ref.Nr.:** UDS000050\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000050\_20150304

(\* Explanation phrases : see chapter 16)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
<b>Contact with skin :</b>	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	If swallowed accidentally, do not induce vomiting and seek medical advice.

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	Irritating to eyes Symptoms : redness and pain

### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes



**Productname :** SERVISOL IPA 170  
**Ref.Nr.:** UDS000050\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000050\_20150304

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.  
Eyewash bottles should be available

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep out of reach of children.

### 7.3. Specific end use(s)

Cleaners - Precision

## SECTION 8: Exposure controls/personal protection



**Productname :** SERVISOL IPA 170  
**Ref.Nr.:** UDS000050\_3\_20170629 (EN) **Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000050\_20150304

## 8.1. Control parameters

### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
carbon dioxide	124-38-9	TWA	9000 mg/m3
		STEL	1800 mg/m3
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm
<b>National established exposure limits, United Kingdom</b>			
carbon dioxide	124-38-9	TWA	5000 ppm
		STEL	15000 ppm
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm

## 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation Wear suitable protective gloves
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A)
<b>hands and skin :</b>	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	(neoprene)
<b>eyes :</b>	Wear safety eyewear according to EN 166.
<b>Environmental protection:</b>	Avoid release to the environment. Collect spillage.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	Liquid under pressure.
<b>colour :</b>	Colorless.
<b>odour :</b>	Alcohol.
<b>pH :</b>	Not applicable.
<b>Boiling point/range :</b>	82 °C
<b>Flash point :</b>	12 °C (Open Cup)



**Productname :** SERVISOL IPA 170  
**Ref.Nr.:** UDS000050\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000050\_20150304

**Explosion limits : upper limit :** 12 %  
**lower limit :** 1.8 %  
**Vapour pressure :** 4.16 kPa (@ 20°C).  
**Relative density :** 0.785 g/cm<sup>3</sup> (@ 20°C).  
**Solubility in water :** Soluble in water  
**Auto-ignition :** 460 °C  
**Viscosity :** Not available.

## 9.2. Other information

**VOC = volatile organic compounds** 794 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO<sub>2</sub>

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

**acute toxicity:** based on available data the classification criteria are not met  
**skin corrosion/irritation:** based on available data the classification criteria are not met  
**serious eye damage/irritation:** Causes serious eye irritation.  
**respiratory or skin sensitisation:** based on available data the classification criteria are not met



**Productname :** SERVISOL IPA 170 **Creationdate :** 29.06.17 Version : 2.0  
**Ref.Nr.:** UDS000050\_3\_20170629 (EN) **Replaces:** UDS000050\_20150304

**germ cell mutagenicity:** based on available data the classification criteria are not met  
**carcinogenicity:** based on available data the classification criteria are not met  
**toxicity for reproduction:** based on available data the classification criteria are not met  
**STOT-single exposure:** May cause drowsiness or dizziness.  
**STOT repeated exposure:** based on available data the classification criteria are not met  
**aspiration hazard:** based on available data the classification criteria are not met

**Information on likely routes of exposure:**

**Inhalation :** Inhalation of solvent vapours may give rise to nausea, headaches and dizziness  
**Ingestion :** May cause gastrointestinal disturbances  
**Skin contact :** May cause irritation.  
**Eye contact :** Irritating to eyes

**Toxicological data :**

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	LD50 oral rat	5840 mg/kg
		LC50 inhal.rat	> 25000 mg/l
		LD50 derm.rabit	13900 mg/kg

**SECTION 12: Ecological information****12.1. Toxicity**

Not classified

**Ecotoxicological data:**

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	1000 mg/l
		LC50 fish	9640 mg/l
		EC50 daphnia	9714 mg/l

**12.2. Persistence and degradability**

No information available

**12.3. Bioaccumulative potential**

No information available

**12.4. Mobility in soil**

Soluble in water



**Productname :** SERVISOL IPA 170  
**Ref.Nr.:** UDS000050\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000050\_20150304

#### 12.5. Results of PBT and vPvB assessment

No information available

#### 12.6. Other adverse effects

No information available

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.  
**National regulations :** Disposal should be in accordance with local, state or national legislation

### SECTION 14: Transport information

#### 14.1. UN number

UN-number : 1950

#### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

#### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

#### 14.4. Packing group

Packing group: Not applicable.

#### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

#### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U





**Productname :** SERVISOL IPA 170  
**Ref.Nr.:** UDS000050\_3\_20170629 (EN) **Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000050\_20150304

IATA/ICAO - PAX: 203  
IATA/ICAO - CAO 203

#### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

#### 15.2. Chemical safety assessment

No information available

### SECTION 16: Other information

\*Explanation hazard statements: H225 : Highly flammable liquid and vapour.  
H280 : Contains gas under pressure; may explode if heated.  
H319 : Causes serious eye irritation.  
H336 : May cause drowsiness or dizziness.

REVISIONS IN CHAPTRE : 8.2. Exposure controls

acronyms and synonyms: TWA = time weight average  
STEL = short time exposure limit  
VOC = volatile organic compounds  
PBT = persistant bioaccumulative toxic  
vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

