


16	HDMI D TYPE Transparent Dust Cover	1	pcs
15	HDMI D TYPE Automatic Welding Under The Tinplate Shell,Nickel Plated	1	pcs
14	HDMI D TYPE Automatic Welding On The Tinplate Shell,Nickel Plated	1	pcs
13	HDMI D TYPE ABS One-Piece Before Head, Colocr: BLACK	1	pcs
12	HDMI D TYPE ABS One-Piece Shell, Colocr: BLACK SR OD: 5.9MM	1	pcs
11	HDMI D TYPE, Automatic Welding Insulation: Black, Pin Gold Plated, Shell Gold Plated	1	pcs
10	HDMI D TYPE 19P M 34AWG Black Double Rows With Tail Clip Wire Frame	1	pcs
9	Black heat-shrinkable tubing thin-wall $\phi$ 1.5*18mm	0.018	m
8	HDMI M Transparent Dust Cover	1	pcs
7	45P PVC, Colocr: Black	20	g
6	Transparent PE Internal Model Materials	8	g
5	Red mere ABS One-Piece Before Head, Colocr: BLACK	1	pcs
4	Red mere ABS One-Piece Shell, Colocr: BLACK	1	pcs
3	Red mere PCB Wire Frame BLACK 36AWG 1.4V	1	pcs
2	Red mere 10.2Gbps PCB+SMT (HDMI Pin Gold Flash, Shell Gold Flash )	1	Set
1	UL20276 [36AWG(7/0.05TC)*1P+EAM]*5C+7/0.05TC*4C+AB (16/9/0.06TC 85%TC) OD:3.6MM BLACK MARKING:HIGH SPEED HDMIR CABLE WITH ETHERNET ...	1.84	m
NO	DESCRIPTION	Q'TY	UNIT



	TOLERANCE				
	INCHES	M/M			
	.X	.015	.30		
	.XX	.010	.10	TITLE: REDMERE HDMI CABLE(10.2G) 36AWG	
	.XXX	.005	.05	CUSTOMER : CPC	
DRAWN BY	Miles		CUSTOMER P/N :		
CHECK BY			SCALE	NONE	DRAWING NO.:
APPD BY			UNIT	MM	REV. A
			DATE	2014.11.04	1/2