

For more Information
please call

1-800-Belden1



General Description:

The insulation is cross-linked polyethylene applied in a single extrusion. This construction has excellent thermal aging characteristics, moisture resistance, and solvent resistance. The 356-series of XL-DUR is recommended for class 130(B) as motor leads

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	16	26x30	TC - Tinned Copper

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Min. Avg. Wall (in.)
XLPE - Cross Linked Polyethylene	0.030

Overall Insulation

Overall Cable

Overall Nominal Diameter: 0.122 in.

Mechanical Characteristics (Overall)

Bulk Cable Weight: 14 lbs/1000 ft.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL Rating:	600 V, 125°C
CSA Rating:	600 V, 125°C
CSA Type:	CL1251
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

4.000

Max. Operating Voltage - UL:

Voltage

600 V

Max. Recommended Current:

Description	Current
Single conductor in free air @ 30C ambient	28 amps

35616 Hook-up/Lead - UL AWM Style 3173 - XL-DUR®

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
35616 0015000	5,000 FT	75.000 LB	BROWN	C I U Z	#16STR XLPE 125C 600VBRN
35616 002500	500 FT	7.500 LB	RED	F	#16 STR XLPE 125C 600V
35616 0025000	5,000 FT	75.000 LB	RED	C I U Z	#16 STR XLPE 125C 600V
35616 0035000	5,000 FT	75.000 LB	ORANGE	C I U Z	#16STR XLPE 125C 600VORG
35616 0045000	5,000 FT	75.000 LB	YELLOW	C I U Z	#16STR XLPE 125C 600VYEL
35616 005500	500 FT	7.500 LB	GREEN, DARK	F	#16 STR XLPE 125C 600V
35616 0055000	5,000 FT	75.000 LB	GREEN, DARK	C I U Z	#16STRXLPE 125C 600VDGRN
35616 0065000	5,000 FT	75.000 LB	BLUE, LIGHT	C I U Z	#16STRXLPE 125C 600VLBLU
35616 009500	500 FT	7.500 LB	WHITE	F	#16 STR XLPE 125C 600V
35616 010500	500 FT	7.500 LB	BLACK	F	#16 STR XLPE 125C 600V
35616 0105000	5,000 FT	75.000 LB	BLACK	C I U Z	#16STR XLPE 125C 600VBLK

Notes:

C = CRATE REEL PUT-UP.

F = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'

I = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 200'

U = TOPCOAT ADDERS ON STOCK SOLID COLORS. MINIMUM ORDER 10000' PER COLORCOMBINATION. (SEE TOPCOAT ADDER TABLE)

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 09-04-2015

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).