

**KEMET Part Number: C0402C471K8RACTU**  
(C0402C471K8RAC7867)

Ceramic, SMD Comm X7R, 470 pF, 10%, 10 V, 0402, X7R, SMD, MLCC, Temperature Stable, Class II



**Dimensions**

Dimension	Value
L	1mm +/-0.05mm
W	0.5mm +/-0.05mm
T	0.5mm +/-0.05mm
S	0.3mm MIN
B	0.3mm +/-0.1mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Paper Tape
<b>Packaging Quantity:</b>	10000

**General Information**

<b>Style:</b>	SMD Chip
<b>Series:</b>	SMD Comm X7R
<b>Chip Size:</b>	0402
<b>Description:</b>	SMD, MLCC, Temperature Stable, Class II
<b>Features:</b>	Temperature Stable, Class II
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Marking:</b>	No
<b>Failure Rate:</b>	N/A
<b>Miscellaneous:</b>	Note: Referee time for X7R dielectric for this part number is 1000 hours

**Specifications**

<b>Capacitance:</b>	470 pF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	10 VDC
<b>Dielectric Withstanding Voltage:</b>	25 V
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	X7R
<b>Dissipation Factor:</b>	5% 1kHz 25C
<b>Aging Rate:</b>	3% Loss/Decade Hour
<b>Insulation Resistance:</b>	100 GOhms