

KEMET Part Number: C1812X224KCRACTU
(C1812X224KCRAC7800)

Ceramic, SMD Comm X7R HV Flex, 0.22 uF, 10%, 500 V, 1812, X7R, SMD, MLCC, FT-CAP, Temperature Stable



Dimensions

L	4.5mm +/-0.4mm
W	3.2mm +/-0.3mm
T	1.7mm +/-0.15mm
B	0.7mm +/-0.35mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	1000

General Information

Style:	SMD Chip
Series:	SMD Comm X7R HV Flex
Chip Size:	1812
Description:	SMD, MLCC, FT-CAP, Temperature Stable
Features:	FT-CAP, Temperature Stable
RoHS:	Yes
Termination:	Flexible Termination
Marking:	No
Failure Rate:	N/A
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours

Specifications

Capacitance:	0.22 uF
Capacitance Tolerance:	10%
Voltage DC:	500 VDC
Dielectric Withstanding Voltage:	750 V
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5% 1kHz 25C
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	455 MOhms