

8458 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1



General Description:

22 AWG stranded (7x30) tinned copper conductors, conductors cabled, PVC insulation, PVC Jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
15	22	7x30	TC - Tinned Copper

Total Number of Conductors: 15

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.011

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.040

Overall Cable

Overall Cabling Color Code Chart:

Color
Black
White
Red
Green
Orange
Blue
White/Black
Red/Black
Green/Black
Orange/Black
Blue/Black
Black/White
Red/White
Green/White
Blue/White

Overall Nominal Diameter: 0.315 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

UL Temperature Rating: 80°C (UL AWM Style 2576)

Bulk Cable Weight: 64 lbs/1000 ft.

Max. Recommended Pulling Tension: 135 lbs.

Min. Bend Radius/Minor Axis: 3.250 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMG

CEC/C(UL) Specification: CMG

8458 Multi-Conductor - Audio, Control and Instrumentation Cable

AWM Specification:	UL Style 2576 (150 V 80°C)
CSA Specification:	FT4
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/ft)	.17
--------------------	-----

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)	34
---------------------	----

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)	15.6
--------------------------	------

Max. Operating Voltage - UL:

Voltage	300 V RMS (CMG)
	150 V RMS (UL AWM Style 2576)

Max. Recommended Current:

Current	2.1 Amps per conductor @ 25°C
---------	-------------------------------

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8458 060100	100 FT	7.300 LB	CHROME		15 #22 PVC PVC
8458 0601000	1,000 FT	72.000 LB	CHROME	C	15 #22 PVC PVC
8458 060500	500 FT	35.500 LB	CHROME	C	15 #22 PVC PVC
8458 0605000	5,000 FT	345.000 LB	CHROME	C	15 #22 PVC PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 08-31-2012

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).