# **Detailed Specifications & Technical Data**

## **ENGLISH MEASUREMENT VERSION**



## 9962 Multi-Conductor - 2 Conductors Cabled-Communication and Instrumentation Cable



For more Information please call

1-800-Belden1



## **General Description:**

20 AWG stranded (19x32) tinned copper conductors, conductors cabled, nylon skin over insulation, PVC insulation, tinned copper braid shield (90% coverage), PVC jacket.

2

## **Physical Characteristics (Overall)**

## Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	20	19x32	TC - Tinned Copper

Total Number of Conductors:

#### Insulation

Insulation Material:

-		Wall Thickness (in.)
1	PVC - Polyvinyl Chloride	0.011
2	Nylon	0.003

Insulation Resistance: 500 megohms/1000 ft. @ 500 VDC

#### **Outer Shield**

Outer Shield Material:



## **Outer Jacket**

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.016

## **Overall Cable**

**Overall Cabling Color Code Chart:** 

	_
Number	Colo
1	White
2	Black

Overall Nominal Diameter:

0.192 in.

## **Mechanical Characteristics (Overall)**

Operating Temperature Range:	-20°C To +105°C
UL Temperature Rating:	105°C
Bulk Cable Weight:	22 lbs/1000 ft.
Max. Recommended Pulling Tension:	30 lbs.
Min. Bend Radius/Minor Axis:	2 in.

## **Applicable Specifications and Agency Compliance (Overall)**

## **Applicable Standards & Environmental Programs**

EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Page 1 of 2 01-05-2017

# **Detailed Specifications & Technical Data**

## **ENGLISH MEASUREMENT VERSION**



## 9962 Multi-Conductor - 2 Conductors Cabled-Communication and Instrumentation Cable

	Military Specification:	MIL-W-16878E/17 (insulated conductor)		
	Other Specification:	NEMA HP3		
Plei	num/Non-Plenum			
	Plenum (Y/N):	No		
-	strice Characteristics (Overall)			

Nom. Inductance:

Inductance (µH/ft) .134

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

Max. Operating Voltage - Non-UL:

Voltage 600 V RMS

Max. Recommended Current:

Current 3.8 Amps per conductor @ 25°C

## **Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9962 009100	100 FT	3.000 LB	WHITE		2 #20 PVC/NY SHLD PVC
9962 0091000	1,000 FT	24.000 LB	WHITE	С	2 #20 PVC/NY SHLD PVC
9962 009500	500 FT	13.000 LB	WHITE		2 #20 PVC/NY SHLD PVC

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 09-10-2012

© 2017 Belden, Inc All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its bublication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Page 2 of 2