Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

SmartPro LCD 120V 1200VA 700W Line-Interactive UPS, AVR, 2U Rack/Tower, LCD, USB, DB9 Serial, 8 **Outlets**

MODEL NUMBER: SMART1200LCD











Description

The SMART1200LCD SmartPro LCD 120V, 1200VA/700W Line-Interactive Uninterruptible Power Supply

provides battery backup and AC power protection against blackouts, brownouts, power surges and line noise that can damage electronics or destroy data.

Ideal for backing up your desktop computer or audio/visual components, this line-interactive UPS switches to battery backup mode in milliseconds to keep your connected equipment running long enough to save files and shut down safely with no data loss.

Eight NEMA 5-15R outlets protect against surges, as well as provide up to 12 minutes of UPS battery support at half load (350W) and 4 minutes of support at full load (700W). Automatic voltage regulation (AVR) corrects severe undervoltages as low as 75V and overvoltages as high as 147V without using any battery power. EMI/RFI noise filtering improves your equipment's performance and prevents damage. A 480-joule surge suppression rating protects your equipment from harmful power surges.

NEMA 5-15P plug with 6-foot cord connects to any NEMA 5-15R socket. Large rotatable LCD screen with dimmer shows real-time input voltage, overload, AVR and battery statuses at a glance. Alarm sounds to indicate power loss or low battery. With Tripp Lite's free PowerAlert software (available via free web download), the SMART1200LCD enables safe unattended system shutdown and file saves in case of a prolonged power failure.

Features

Reliable Battery Backup

- Provides 1200VA/700W high-performance power protection for desktop computers, audio/video components, media centers and other electronics
- Supports 50% load (350W) up to 12 minutes and full load (700W) up to 4 minutes
- · Audible alarm indicates loss of utility power or low battery

Optimized Outlets

8 NEMA 5-15R outlets provide battery backup and protect against surges or spikes that can harm equipment or data

Automatic Voltage Regulation (AVR)

Highlights

- Supports a half-load (350W) up to 12 min. during power outage
- Supports a full load (700W) up to 4 min. during power outage
- Features 8 protected NEMA 5-15R outlets
- Offers automatic voltage regulation (AVR)
- · LCD screen reports real-time UPS and power status

Package Includes

- SMART1200LCD SmartPro LCD 120V 1000VA/500W Line-Interactive UPS
- USB cable
- DB9 serial cable
- Telephone cable
- Mounting hardware
- Owner's Manual

1/5



• Corrects undervoltages as low as 75V and overvoltages as high as 147V without drawing battery backup power

Rotatable LCD Status Screen

- Large LCD screen shows real-time input voltage, overload, AVR and battery statuses
- Rotates for easy viewing in both horizontal and vertical installations
- Dimmer switch controls brightness level

AC Line, Tel/DSL and Ethernet Surge Suppression

- Surge suppression rating of 480 joules protects connected equipment and data from harmful power surges
- Built-in RJ-45 jacks protect single-line tel/DSL or network Ethernet connection

EMI/RFI Line Noise Filtering

• Removes electromagnetic and radio frequency interference that can disrupt or damage your equipment's performance

USB and DB9 Communication Ports and Free PowerAlert Software

- HID-compliant USB port integrates with built-in power management and auto-shutdown of Windows and Mac OS X
- USB and DB9 serial ports work with Tripp Lite PowerAlert software (available for free download at www.tripplite.com/poweralert) to enable safe, unattended system shutdown and file saves during prolonged power failure

Flexible Installation Options

- NEMA 5-15P plug with 6-foot cord connects to any NEMA 5-15R socket
- Adapts to vertical or horizontal installation without special hardware
- Includes 2U brackets for rack-mount installation

Specifications

OUTPUT		
Output Volt Amp Capacity (VA)	1200	
Output kVA Capacity (kVA)	1.2	
Output Watt Capacity (Watts)	700	
Nominal Output Voltage(s) Supported	110V; 115V; 120V	
Nominal Voltage Details	115v nominal output in battery mode	
Frequency Compatibility	60 Hz	
Output Voltage Regulation (Line Mode)	-18%, +8%	
Output Voltage Regulation (Battery Mode)	+/- 5%	
Output Receptacles	(8) 5-15R	
Output AC Waveform (AC Mode)	Sine wave	
Output AC Waveform (Battery Mode)	PWM sine wave	





INPUT		
Rated input current (Maximum Load)	7A	
Nominal Input Voltage(s) Supported	120V AC	
UPS Input Connection Type	5-15P; Right-Angled	
Input Circuit Breakers	10A	
UPS Input Cord Length (ft.)	6	
UPS Input Cord Length (m)	1.8	
Recommended Electrical Service	15A 120V	
Input Phase	Single-Phase	
BATTERY		
Full Load Runtime (min.)	4 min. (700w)	
Half Load Runtime (min.)	12 min. (350w)	
DC System Voltage (VDC)	24	
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%	
Expandable Runtime	No	
VOLTAGE REGULATION		
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 75 to 147	
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%	
Undervoltage Correction	Input voltages between 93 and 107 are boosted by 14%	
Severe Undervoltage Correction	Input voltages between 75 and 92 are boosted by 30%	
USER INTERFACE, ALERTS & CONTROLS		
Front Panel LCD Display	Backlighted LCD screen indicates input voltage, 5-bar battery charge level, overload, AVR, on battery and replace battery status; LCD screen rotates for rack/tower viewing	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; dimmer switch controls LCD brightness	
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status	
Audible Alarm	Audible alarm indicates power-failure and low-battery status; alarm can be disabled using PowerAlert software	
LED Indicators	Front panel LCD display	
SURGE / NOISE SUPPRESSION		
UPS AC Suppression Joule Rating	480	
UPS AC Suppression Response Time	Instantaneous	





UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet	
EMI / RFI AC Noise Suppression	Yes	
PHYSICAL		
Included Mounting Accessory Description	Pair of mounting ears enable tower and 2-4 post rackmount installation	
Primary Form Factor	Rackmount	
UPS Power Module Dimensions (hwd, in.)	3.5 x 17.25 x 10.5	
UPS Power Module Dimensions (hwd, cm)	8.9 x 43.8 x 26.7	
Rack Height (U Spaces)	2	
Minimum Required Rack Depth (inches)	13.5	
Minimum Required Rack Depth (cm)	34.29	
UPS Power Module Weight (lbs.)	29.4	
UPS Power Module Weight (kg)	13.34	
UPS Shipping Dimensions (hwd / in.)	7.5 x 15 x 21.5	
UPS Shipping Dimensions (hwd / cm)	19 x 38.1 x 54.6	
Shipping Weight (lbs.)	29.4	
Shipping Weight (kg)	13.3	
UPS Housing Material	ABS	
Minimum Required Rack Depth (mm)	343	
Primary UPS Height (mm)	89	
Primary UPS Width (mm)	438	
Primary UPS Depth (mm)	267	
Shipping Height (mm)	190	
Shipping Width (mm)	381	
Shipping Depth (mm)	546	
ENVIRONMENTAL		
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius	
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius	
Relative Humidity	0 to 95%, non-condensing	
AC Mode BTU / Hr. (Full Load)	180	
Battery Mode BTU / Hr. (Full Load)	490	





AC Mode Efficiency Rating (100% Load)	93%
COMMUNICATIONS	
Communications Interface	USB (HID enabled); DB9 Serial
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	USB and DB9 Serial cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	75
High Voltage Transfer to Battery Power (Setpoint)	147
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
WARRANTY	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

https://www.tripplite.com/products/product-certification-agencies