

PTH05050

5 Vin Single Output

Data Sheet

Total Power: 21.6 Watts **Input Voltage:** 4.5 - 5.5 Vdc **# of Outputs:** Single

SPECIAL FEATURES

- 6 A output current
- 5 V input voltage
- Wide-output voltage adjust (0.8 V - 3.6 V)
- Auto-track[™] sequencing*
- Pre-bias start-up capability
- Efficiencies up to 95%
- Output ON/OFF inhibit
- Output voltage sense
- Point-of-Load-Alliance (POLA) compatible
- RoHS compliant
- Two year warranty

SAFETY

- UL/cUL CAN/CSA-C22.2 No. 60950-1-03/UL 60950-1, File No. E186249
- TÜV Product Service (EN60950)
 Certificate No. B 06 07 38572 068





Electrical Specifications							
Input							
Input voltage range	(See Note 3)	4.5 - 5.5 Vdc					
Input current	No load	10 mA typical					
Remote ON/OFF	(See Note 1)	Positive logic					
Start-up time		1 V/ms					
Undervoltage lockout		3.7 - 4.3 Vdc typical					
Track input voltage	Pin 2 (See Notes 6 & 7)	±0.3 Vin					
Output							
Voltage adjustability	(See Note 4)	0.8 - 3.6 Vdc					
Setpoint accuracy		±2.0% Vo					
Line regulation		±10 mV typical					
Load regulation		±12 mV typical					
Total regulation		±3.0% Vo					
Minimum load		0 A					
Ripple and noise	20 MHz bandwidth	20 mV pk-pk					
Temperature co-efficient	-40 °C to +85 °C	±0.5% Vo					
Transient response	(See Note 5)	70 µs recovery time Overshoot/undershoot 100 mV					

All specifications are typical at nominal input, full load at 25 °C unless otherwise stated. Cin = 100 μF , Cout = 0 μF .



^{*}Auto-track is a trademark of Texas Instruments.

General Specifi	cations	
Efficiency	(See Efficiency Table)	95% max.
Insulation voltage		Non-isolated
Switching frequency		550 - 650 kHz
Approvals and standards		EN60950, UL/cUL60950
Material flammability		UL94V-0
Dimensions	LxWxH	22.10 x 12.57 x 8.50 mm 0.870 x 0.495 x 0.335 in
Weight		2.9 g (0.10 oz)
MTBF	Telcordia SR-332F	7,092,000 hours

11 11 1

EMC Characteristics						
Electrostatic discharge	EN61000-4-2, IEC801-2					
Conducted immunity	EN61000-4-6					
Radiated immunity	EN61000-4-3					

Environmental Specifications							
Thermal performance (See Note 2)	Operating ambient temperature Non-operating temperature	-40 °C to +85 °C -40 °C to +125 °C					
MSL ('Z' suffix only)	JEDEC J-STD-020C	Level 3					
Protection							
Short-circuit	Auto reset	12 A typical					

Ordering Information								
Model Number ⁽⁹⁾				Efficiency (Typical)	Regula Line	tion ⁽²⁾		
PTH05050	21.6 W	4.5 - 5.5 Vdc	0.8 - 3.6 V	0 A	6 A	95%	±10 mV	±12 mV

Part Number System with Options

Product Family	Input Voltage	Output Current	Mechanical Package	Output Voltage Code	Pin Option ⁽⁸⁾	Mounting Options	Pin Option
PTH	05	05	0	W	Α	S	Т
Point-of-Load Alliance compatible	05 = 5 V	05 = 6 A	Always 0	W = Wide		D = Horizontal through- hole (RoHS 6/6) Z = Surface-mount solder ball (RoHS 6/6)	No Suffix = Trays T = Tape and Reel ⁽⁸⁾


Output Voltage Adjustment

The ultra-wide output voltage trim range offers major advantages to users who select the PTH05050. It is no longer necessary to purchase a variety of modules in order to cover different output voltages. The output voltage can be trimmed in a range of 0.8 Vdc to 3.6 Vdc. When the PTH05050 converter leaves the factory the output has been adjusted to the default voltage of 0.8 V.

Efficiency Table (lo	= 10 A)
Output Voltage	Efficiency
Vo = 1.0 V	85%
Vo = 1.2 V	87%
Vo = 1.5 V	89%
Vo = 1.8 V	90%
Vo = 2.0 V	91%
Vo = 2.5 V	93%
Vo = 3.3 V	95%

Notes:

- 1. Remote ON/OFF. Positive Logic ON: Pin 3 open; or V > Vin 0.5 V OFF: Pin 3 GND; or V < 0.8 V (min 0.2 V).
- 2. See Figures 1 for safe operating curves.
- A 100 µF electrolytic input capacitor is required for proper operation. The capacitor must be rated for a minimum of 300 mA rms of ripple current.
- 4. An external output capacitor is not required for basic operation. Adding 100 μ F of distributed capacitance at the load will improve the transient response.
- 5. 1 A/ μ s load step, 50 to 100% lomax, Cout = 100 μ F.
- 6. If utilized Vout will track applied voltage by ± 0.3 V (up to Vo set point).
- 7. The pre-bias start-up feature is not compatible with Auto-TrackTM. This is because when the module is under Auto-TrackTM control, it is fully active and will sink current if the output voltage is below that of a back-feeding source. Therefore to ensure a pre-bias hold-off, one of the following two techniques must be followed when input power is first applied to the module. The Auto-TrackTM function must either be disabled, or the module's output held off using the Inhibit pin. Refer to Application Note 158 for more details.
- 8. Tape and reel packaging only available on the surface-mount versions.
- NOTICE: Some models do not support all options. Please contact your local Artesyn
 representative or use the on-line model number search tool at http://www.artesyn.com/power
 to find a suitable alternative.



tp tp tp

90 **EFFICIENCY (%)** 80 - 3.3V ___ 2.5V 70 -- 1.8V 1.2V 60 50 40 0 1 2 3 4 5 6 **OUTPUT CURRENT (A)**

100

Figure 1 - Safe Operating Area
Vin = 5 V, Output Voltage = 3.3 V (See Note A)

Figure 2 - Efficiency vs Load Current Vin = 5 V (See Note B)





Figure 3 - Standard Application


Notes:

- A. SOA curves represent the conditions at which internal components are within the Artesyn derating guidelines.
- B. Characteristic data has been developed from actual products tested at 25 °C. This data is considered typical data for the converter.

Mechanical Drawings

Plated through-hole






Pin	Assignments				
Pin	Function				
1	Ground				
2	Track				
3	Vin				
4	Inhibit*				
5	Vo adjust				
6	Vout				
*Denotes negative logic:					

Open = Normal operation Ground = Function active

Dimensions in Inches (mm)
Tolerances (unless otherwise specified)
2 Places 0.030 (0.76)
3 Places 0.010 (0.25)

Surface-mount



11 11 11

Dimensions in Inches (mm)
Tolerances (unless otherwise specified)
2 Places 0.030 (0.76)
3 Places 0.010 (0.25)

WORLDWIDE OFFICES

Americas

2900 S.Diablo Way Tempe, AZ 85282 USA +1 888 412 7832

Europe (UK)

Waterfront Business Park Merry Hill, Dudley West Midlands, DY5 1LX United Kingdom +44 (0) 1384 842 211

Asia (HK)

14/F, Lu Plaza 2 Wing Yip Street Kwun Tong, Kowloon Hong Kong +852 2176 3333



www.artesyn.com

For more information: www.artesyn.com/power For support: productsupport.ep@artesyn.com

While every precaution has been taken to ensure accuracy and completeness in this literature, Artesyn Embedded Technologies assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions. Artesyn Embedded Technologies, Artesyn and the Artesyn Embedded Technologies logo are trademarks and service marks of Artesyn Embedded Technologies, Inc. All other names and logos referred to are trade names, trademarks, or registered trademarks of their respective owners. © 2015 Artesyn Embedded Technologies, Inc.