



- † Red band indicates fully mated
- †† Blue band indicates rear release contact retention system
- ★ .059 dia min.
- 1.5 dia min., 3 lockwire holes formed lockwire hole design (6 holes) is optional

Note: -Drawing not to Scale
 -Dimensions subject to change
 -Dimensions are in Inches, Millimeters (MM) & Blue color
 Property of Amphenol Aerospace.
 All rights reserved.

Part No.:
D38999/24ZH35BN

Amphenol
 Aerospace
 40-60 Delaware Avenue
 Sidney, NY 13838-1395
 800-678-0141
 Cage Code: 77820
www.amphenol-aerospace.com



Amphenol Aerospace
 40-60 Delaware Avenue
 Sidney, NY 13838-1395
Phone: 800-678-0141 - **Fax:** 607-563-5157
Email: info@amphenol-aerospace.com
Website: www.amphenol-aerospace.com

Joe Ryder
 Product Line Manager
 Core Products
Phone: 607-563-5001
Email: jryder@amphenol-ao.com

Specifications

| | |
|-----------------------------|-------------------------------|
| Connector Type | D38999/ |
| Shell Style | Jam Nut Receptacle |
| Shell Material | Aluminum |
| Shell Finish | Black Zinc-Nickel Plated |
| Insulation Resistance | 5000 megohms min. @500 VDC25C |
| Operating Temperature [Min] | -65°C |
| Operating Temperature [Max] | +175°C |
| Shielding Effectiveness | 50dB@10GHz |
| Durability | 500 Hour Salt Spray |
| Contact Type | B |
| Contact Description | Less Sockets |

Contacts

| | |
|--------------------------------|----------------|
| Insert Arrangement | |
| Front Face of Pin Insert Shown | |
| Shell Size | H |
| Insert Arrg | 35 |
| Service Rating | M |
| Total # Contacts | 100 |
| Test Current | 5 AMPS |
| Wire Size for 22D | 28, 26, 24, 22 |
| Contact Size 22D | 100 |
| Number of Contacts | |