







OVERVIEW:

The CM-2400 is a professional-grade condenser microphone with a large diaphragm. It utilizes an extremely accurate electronic circuit control, and a beautifully constructed capsule. The CM-2400 is a high output, low noise design that provides fantastic reproduction down to the most subtle of sounds. It also features three polar-patterns (uni, bi, and omni-directional) that are switchable via a switch on the front of the microphone. The CM-2400 is best suited for: Studio recording, broadcasting, and high-fidelity recording.



Specifications:

- Element: 34 Pressure Gradient Transducer
- Polar Pattern: Uni/Bi/Omni-directional
- Frequency Response: 20Hz-20kHz
- Sensitivity: -31dB/-34dB/-35dB±2dB (0dB=1V/Pa at 1kHz)
- Output Impedance: 200Ω±30% (at 1kHz)
- S/N Ratio: 80/79/78dB
- Phantom Power Requirement: 48V DC Phantom



Warranty

This device is warranted against manufacturer defects for a period of one year from the date of purchase from the dealer. This warranty extends solely to the repair or replacement of this product and does not cover additional costs, including but not limited to installation or removal of the product or any incidental or consequential damages. Nor does it cover damage due to improper use, storage or application of this device. Should a service issue arise within the one year period, please contact the dealer in which this device was purchased. It will be the sole decision of Stellar Labs to repair or replace any device found to be defective during this period.

Distributed exclusively by:
MCM Electronics
www.mcmelectronics.com