

16-Port USB PS/2 Combo KVM Switch with USB KVM Cables

GCS1716KITU



- Multi platform OS support - Windows®, Mac, Sun Solaris™ , and Linux®
- Easy to operate - computer selection via front panel LED's, intuitive OSD (on screen display), and hotkeys
- *Cascade up to 2 levels - control up to 256 computers from a single console
- Security - 2 level password protection for OSD
- Maximum video resolution: up to 2048 x 1536
- ** Front USB Port - Fully compliant with USB 1.1 for system upgrades and shared peripherals
- Rack mountable in a 19" (1U) system rack
- Custom ASIC provides an auto-sensing function that recognizes the position of each station on the installation
- Fully Supports DDC2B

*(Firmware update is now available at <http://www.iogear.com/support/dm/>)

** Only systems connected with the USB KVM cables will be able to access the front USB port for system upgrades and shared peripherals

The GCS1716KITU KVM is a combo switch with USB KVM cables included; allowing access and control of up to 16 directly connected computers from a single console (keyboard, mouse, and monitor). As many as 16 additional switches can be cascaded bringing the total number of connected computers to 256 computers that can be controlled from a single keyboard-monitor-mouse console. A custom ASIC (patent pending) provides an auto-sensing function that recognizes the position of each station on the installation, eliminating the need to manually set the position with DIP switches. Additionally, the GCS1716 features high density SPHD 15-pin instead of the usual 25-pin connectors thus allowing for a compact design and installation in a 1U system rack.

The GCS1716 includes one USB port located on the front panel for easy access and sharing of any USB peripherals. Setup is fast and easy; plugging cables into their appropriate ports is all that is needed. The switch supports both USB and PS/2 connections for the console and computers. The GCS1716 intercepts keyboard input directly, thus eliminating the need for any software configuration. Switching between computers can be easily accomplished either by manually pressing the front panel push button port LEDs, entering hotkey combinations from the keyboard, or via a menu driven multilingual on-screen display (OSD) system. A convenient auto-scan feature permits automatic scanning and monitoring of activities on all connected.




GCS1716KITU Included Cables:

- 16 x 10ft (3M) USB KVM cable (G2L5203U)

Benefits:

- Eliminates the excessive expense of additional monitors, keyboards and mice
- Increases office space, productivity, and provides as an energy cost savings solution
- It contributes to a greener environment by reducing the amount of waste generated by multiple components
- An easy / efficient way to organize and streamline a growing or expanding server operation

16-Port USB PS/2 Combo KVM Switch with USB KVM Cables



Requirements:

Console:

- VGA, SVGA, or MultiSync Monitor
- A Keyboard and Mouse (USB or PS/2)

Computers:

- VGA, SVGA, or MultiSync video graphics card with an HDB-15 port
- PS/2 mouse and keyboard ports (6-pin mini DIN) and at least 1 USB port
- Multi OS Platform Support: PC / Mac / Sun / Linux

Package Contents:

- 1 x GCS1716, 16-Port Combo KVM
- 1 x 2M USB KVM cable (G2L5202U)
- 1 x 2M PS/2 KVM cable (G2L5202P)
- 16 x 3M USB KVM cable (G2L5203U)
- 1 x Console cable
- 1 x Cascade cable
- 1 x Firmware upgrade cable
- 1 x Grounding wire
- 1 x Foot pad set (4 pads)
- 1 x Power adapter
- 1 x Installation Guide
- 1 x Warranty Card
- 1 x Standard Rack Mounting Kit

16-Port USB PS/2 Combo KVM Switch with USB KVM Cables

SPECIFICATIONS

Function	
Computer Connections	
Direct	16
Daisy Chain or Cascading	256 (via Cascade)
Port Selection	Hotkeys, OSD, Button
Connectors	
Console	1 x SPHD-18 Male (Yellow)
Computer/KVM	16 x SPHD-15 Female (Yellow)
Power	1 x DC Jack
USB	1 x USB 1.1 Type A Female
Reset Switch	1 x Semi-Recessed Push Button
Switches	
F/W Upgrade	1 x Slide Switch
Port Selection	16 x Push Button
Emulation	
Keyboard	PS/2, USB
Mouse	PS/2, USB
Video Resolution	VGA 2048x1536, DDC2B
Power	
Voltage	DC 5.3V
Amps	2.4A
Scan Interval	1-255 sec
Environment	
Operation Temperature	0~50C
Storage Temperature	-20~60C
Humidity	0~80% RH, Non-condensing
Housing	
Case	Metal

Dimensions	
Unit Dimensions	
Width	17in.
Height	1.75in.
Depth	6.25in.
Unit Package Dimensions	
Width	10.25in.
Height	9.625in.
Depth	22.375in.
Weight	
Unit Pack Wt.	20.04lb
Unit Wt. w/accessories	17.26lb
Unit Wt.	6.02lb