



Features:

- Universal / Full Range Input
- Interchangeable AC Heads
- Level 6 Efficiency
- Cost Effective & Highly Reliable
- 1 Year Warranty



| Characteristics | | |
|--------------------------|--|--------------|
| Part Number | T5776ST | T5778ST |
| Model Designation | 6A-401WP | |
| Output Voltage | 12Vdc | 24Vdc |
| Output Current Max | 3A | 1.7A |
| Output Current Min | 0A | 0A |
| Power (Watts) | 36W | 40W |
| Line Regulation | +/- 1% | |
| Voltage Tolerance | +/- 5% | |
| Ripple & Noise (mV p-p) | <120mV (p-p) | <200mV (p-p) |
| Protections | Over Voltage Protection Short Circuit Protection Over Load Protection | |
| Rated Input Voltage | 100 - 240Vac | |
| Full Input Voltage Range | 90Vac - 264Vac | |
| Rated Frequency | 50 - 60Hz | |
| Full Frequency Range | 47 - 63Hz | |
| Efficiency | 87.4% | 87.6% |
| Input Current (RMS Max) | 1A | |
| Inrush Current | No Damage | |
| Leakage Current | <0.25mA | |
| Input Power (no load) | <0.1W | |
| AC Inlet | Interchangeable UK, Euro & US Plugtop | |
| DC Cord | 1.5M Cable | 1.5M Cable |
| DC Plug | 2.1mm C+Ve | 2.1mm C+Ve |
| Hi-Pot Specification | 3000Vac or 4242Vdc 10mA 1 min. (I.P. to O.P.) | |
| Insulation Resistance | 500Vdc to test the I.P.-O.P resistance is not less than 100Mohm (I.P. to O.P.) | |
| Operating Temperature | 0C to 40C | |
| Storage Temperature | -10C to 70C | |
| Operating Humidity | 20 % to 80% | |
| Storage Humidity | 10% to 90% | |
| Safety Approvals | UL/CUL, CE, CB, GS, RCM, | |
| PB-Free | Yes - RoHS Compliant | |
| Dimensions (mm) | 90 x 38 x 59.4 | |

Stontronics Ltd

Chancerygate Business Centre, Cradock Road, Reading, Berkshire, RG2 0AH.

Tel: +44 (0) 118 931 1199 • Fax: +44 (0) 118 931 1145 • Email: info@stontronics.co.uk • Web: www.stontronics.com

Please Note: Image shown is representative of entire range. Individual PSU image &/or drawings or data sheets available on request.

Stontronics Ltd accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice.

