

Mobile work lamps with super-bright SMD LEDs

Mobile SMD LED lamp ML DN 2806 S IP54 / ML DN 4006 S IP54 1173823 / 1173833

Characteristics

- High-quality SMD LEDs from LG Innotek
- Casing made of aluminum pressure casting, surface coated.
- Stable frame.
- Carrying handle with foam grip
- On/Off switch for light on the back.
- Floodlight can be pivoted and locked in place steplessly.
- Front pane made of safety glass.




ML DN 2806 S IP54




ML DN 4006 S IP54



Rear view



LED:  LG Innotek



Technical highlights

- Brand-name SMD LEDs from LG Innotek with a high degree of efficiency
- GS-certified product



Specifications

- Type of protection: IP 54
- Energy efficiency class: A
- Supply voltage: 220-240 V~ 50/60 Hz
- Color temperature: 5700 K
- LED service life: 50,000 hrs
- Radiation angle: approx. 110°
- Protection class: I
- Connection cable: 2m H05RN-F3G1,0
- Dimensions: 215 x 215 x 325 mm
- Weight: approx. 1.85 kg