


KEMET Part Number: PHE450PD6220JD16R30
(F450DT224J1K0ALW0L)

PHE450/F450, Film, Double Metallized Polypropylene, Commercial Grade, 0.22 uF, 5%, 1,000 V, 85C, Lead Spacing = 22.5mm



General Information	
Supplier:	KEMET
Series:	PHE450/F450
Dielectric:	Double Metallized Polypropylene
Style:	Radial
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	The Rated Voltage Decreases 1.3%/C Between +85C And +105C. Rthha= 44 C/W (85C), 0.2 m/s

Dimensions	
L	26mm MAX
H	21.5mm MAX
T	11mm MAX
S	22.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Specifications	
Capacitance:	0.22 uF
Capacitance Tolerance:	5%
Voltage DC:	1000 VDC (85C), 740 VDC (105C)
Voltage AC:	600 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.03% 1kHz, 0.06% 10kHz
Insulation Resistance:	100 GOhms
Max dVdt:	1,800 V
Inductance:	6 nH

Packaging Specifications	
Packaging:	Bulk, Bag

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.