

ZCKE21

limit switch head ZCKE - thermoplastic roller lever plunger



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ4H7 ZCKJ8 ZCKJD31H29 ZCKJ21H29 ZCKJ4 ZCKJD37 ZCKJ6H29 ZCKJD39H7 ZCKJ4H29 ZCKJ41H7 ZCKJ21 ZCKJ2H7 ZCKJD35H29 ZCKJ7H29 ZCKJ8H29 ZCKJD31 ZCKJ9H7 ZCKJD39H29 ZCKJ1 ZCKJ1H7 ZCKJD35H7 ZCKJD39 ZCKJD37H7 ZCKJ1H29 ZCKJ11H7 ZCKJ5 ZCKJ5H7 ZCKJ9H29 ZCKJ41 ZCKJ2H29 ZCKJ41H29

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKJD31H7
 ZCKJD37H29
 ZCKJ6H7
 ZCKJ6
 ZCKJ21H7
 ZCKJ5H29
 ZCKJ11
 ZCKJ8H7
 ZCKJD35
 ZCKJ11H29
 ZCKJ2
 ZCKJ7H7
 ZCKJ7
 ZCKJ9

Movement of operating head	Linear Rotary
Type of operator	Roller lever plunger spring return thermoplastic
Type of approach	Lateral approach 1 direction

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1012 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------