

Data Sheet

RP018xxVBLC

Page 1/5


P/N

312621xx

xx=number of poles

2017/01/24

Illustration



see enlarged drawing at the end of the document

Product specification

- screw type terminal block, pluggable
- centerline 7.62 mm, direction of connection vertical 0°
- lift system, fittable without loss of poles
- color black
- wire entry codeable side perpendicular to plug direction

Data Sheet

RP018xxVBLC

Technical Data

General Data

Tightening torque SEV	0.5 Nm		
Tightening torque UL	4.5 lb-in		
min. number of poles	2		
max. number of poles	12		
Insulating material class	CTI 600		
clearance/creepage dist.	6.1 mm		
protection category	IP 20		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	400 V	1000 V	1000 V
Rated test voltage	6.0 kV	6.0 kV	6 kV


Connection data

Rated wiring solid wire	0.08 - 2.0 mm ² / AWG 28 - 14		
Rated wiring stranded wire	0.08 - 2.0 mm ² / AWG 28 - 14		

Approvals

extended wiring UL	2 AWG 16-18, or 1 AWG 16 stranded with 1 AWG 18 solid, or 1 AWG 16 stranded with 1 AWG 18 stranded		
--------------------	--	--	--

 V / A / AWG	300 / 15 / 28 - 14		
--	--------------------	--	--

 SEV	13.5 A / 500 V / 6 kV / 3 / IEC 61984 / 0.08 - 2.5 mm ²		
--	---	--	--

Material

insulating material	PA66
flammability class	V0
contact material	CuSn
Glow-Wire Flammability GWFI	960
Glow-Wire Flammability GWIT	775
contact surface	Sn
terminal body material	CuZn
terminal body surface	Ni
screw surface	Zn Cr(VI)-frei/free
screw thread	M3

Climatic properties

upper limit temperature	105 °C
lower limit temperature	-40 °C

Data Sheet

RP018xxVBLC

Page 3/5

P/N

312621xx

xx=number of poles

2017/01/24

General

Tolerance	ISO 2768 -mH
-----------	--------------



Data Sheet

RP018xxVBLC

Page 4/5

P/N

312621xx

xx=number of poles

2017/01/24

Matching Part

P/N	Product name
312631	PT118xxVBEC Typ 263
312641	PT118xxVBBC Typ 264
312651	PT118xxHBEC Typ 265
312661	PT118xxHBBC Typ 266

Accessories

P/N	Product name
700025-01-9	700025

Data Sheet

RP018xxVBLC

Page 5/5

P/N


312621xx

xx=number of poles

2017/01/24

Illustration

Drawing



$$L = (\text{pole size} - 1) \times \text{centerline} + 5.62 [0.221]$$

