


F464, Film, Metallized Polypropylene, Commercial Grade, 0.47 uF, 5%, 2,500 V, 85C, Lead Spacing = 37.5mm



General Information	
Supplier:	KEMET
Series:	F464
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	MKP, Pulse
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	The Rated Voltage Decreases 2%/C Between +85C And +105C (1.25%/C For AC). ClimCat: 55/105/56

Dimensions	
L	41mm MAX
H	45mm MAX
T	30mm MAX
S	37.5mm +/-0.4mm
LL	17mm -1mm
F	1mm +/-0.05mm
G	0.5mm NOM

Specifications	
Capacitance:	0.47 uF
Capacitance Tolerance:	5%
Voltage DC:	2500 VDC, 1500 VDC (105C)
Voltage AC:	900 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.05% 1kHz, 0.06% 10kHz
Insulation Resistance:	63.8298 GOhms
Max dVdt:	900 V
Inductance:	6 nH

Packaging Specifications	
Packaging:	Pizza, Box
Packaging Quantity:	77