

SMD Auto COG HV, Ceramic, 100 pF, 5%, 3,000 V, COG, SMD, MLCC, Ultra-Stable, Low Loss, Automotive Grade, 1812



Dimensions

| | |
|----------|-----------------|
| L | 4.5mm +/-0.3mm |
| W | 3.2mm +/-0.3mm |
| T | 1.6mm +/-0.20mm |
| B | 0.6mm +/-0.35mm |

Packaging Specifications

| | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 1000 |

General Information

| | |
|----------------------|-----------------------------------------------------|
| Supplier: | KEMET |
| Series: | SMD Auto COG HV |
| Style: | SMD Chip |
| Description: | SMD, MLCC, Ultra-Stable, Low Loss, Automotive Grade |
| Features: | Ultra-Stable, Low Loss, Automotive Grade |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Failure Rate: | N/A |
| Approvals: | AEC-Q200 |
| AEC-Q200: | Yes |
| Chip Size: | 1812 |

Specifications

| | |
|-----------------------------------------|---------------------|
| Capacitance: | 100 pF |
| Capacitance Tolerance: | 5% |
| Voltage DC: | 3000 VDC |
| Dielectric Withstanding Voltage: | 3,600 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | COG |
| Dissipation Factor: | 0.1% 1MHz 25C |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.