



Heat Shrinkable Tubing 3:1 in a Kit

ShrinkKit 321 Basic - black

The compact and handy kit belongs to the basic equipment for every assembler. Its ideal shrink ratio of 3:1 replaces many differently sized tubing.

Features and Benefits

- Compact and handy kit
- Black tubing
- Application range from 1 mm to 16 mm
- 220 precut pieces in five sizes



ShrinkKit 321 Basic.



Detailed Information about Heatguns please refer to page 529.

MATERIAL	Polyolefin, cross-linked (PO-X)
Shrink Ratio	3:1
Operating Temperature	-55 °C to +135 °C
Minimum Shrink Temperature	+90 °C
Longitudinal change after shrinkage	+5 %/-10 % max.
Dielectric Strength	20 kV/mm according to ASTM D 2671
Flammability	Self extinguishing
Insulation Class	B (VDE 0530)
Specifications	SAE - AMS - DTL-23053/5 Class 1



Heat Shrinkable Tubing 3:1

RoHS ✓

COMP.	Supplied Ø D min.	Recov. Ø d max.	Length (L)	Wall (WT)	Colour	Content (pcs.)	Article-No.
1	1.5	0.5	35.0	0.45	Black (BK)	50	380-03001
2	6.0	2.0	35.0	0.70	Black (BK)	30	
3	3.0	1.0	35.0	0.55	Black (BK)	25	
4	6.0	2.0	35.0	0.70	Black (BK)	15	
5	6.0	2.0	35.0	0.70	Black (BK)	15	
6	3.0	1.0	35.0	0.55	Black (BK)	25	
7	1.5	0.5	35.0	0.45	Black (BK)	50	
8	12.0	4.0	80.0	0.70	Black (BK)	5	
	18.0	6.0	80.0	0.80	Black (BK)	5	

All dimensions in mm. Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.