Product data sheet Characteristics

LC1F330

TeSys F contactor - 3P(3 NO) - AC-3 - <= 440 V 330 A - without coil





Range	TeSys	
Product name	TeSys F	
Product or component type	Contactor	
Device short name	LC1F	
Contactor application	Resistive load Motor control	
Utilisation category	AC-4 AC-3 AC-1	
Poles description	3P	
Pole contact composition	3 NO	
[Ue] rated operational voltage	<= 1000 V AC 50/60 Hz <= 460 V DC	
[le] rated operational current	400 A (<= 40 °C) at <= 440 V AC AC-1 330 A (<= 55 °C) at <= 440 V AC AC-3	
Motor power kW	160 kW at 380400 V AC 50/60 Hz AC-3 200 kW at 500 V AC 50/60 Hz AC-3 180 kW at 415 V AC 50/60 Hz AC-3 200 kW at 440 V AC 50/60 Hz AC-3 160 kW at 1000 V AC 50/60 Hz AC-3 59 kW at 400 V AC 50/60 Hz AC-4 100 kW at 220240 V AC 50/60 Hz AC-3 220 kW at 660690 V AC 50/60 Hz AC-3	

Complementary

[Uimp] rated impulse withstand voltage	8 kV	.9
Overvoltage category	III	
[lth] conventional free air thermal current	400 A at <= 40 °C	
Irms rated making capacity	3300 A AC conforming to IEC 60947-4-1	É
Rated breaking capacity	2640 A conforming to IEC 60947-4-1	

[lcw] rated short-time withstand current	2650 A <= 40 °C 10 s 1800 A <= 40 °C 30 s 1300 A <= 40 °C 1 min 900 A <= 40 °C 3 min 750 A <= 40 °C 10 min
Associated fuse rating	400 A aM at <= 440 V 500 A gG at <= 440 V
Average impedance	0.28 mOhm at 50 Hz - Ith 400 A
[Ui] rated insulation voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C
Power dissipation per pole	31 W AC-3 44 W AC-1
Mounting support	Plate
Standards	EN 60947-4-1 JIS C8201-4-1 EN 60947-1 IEC 60947-4-1 IEC 60947-1
Product certifications	CSA RINA RMRoS LROS (Lloyds register of shipping) UL ABS CB DNV BV
Connections - terminals	Power circuit : lugs-ring terminals 1 cable(s) 240 mm² Power circuit : bar 2 x (30 x 5 mm)
Tightening torque	Power circuit : 35 N.m

Environment

IP20 front face with shrouds (ordered separately) conforming to IEC 60529 IP20 front face with shrouds (ordered separately) conforming to VDE 0106	
TH	
-555 °C	
-6080 °C	
-4070 °C	
3000 m without derating in temperature	
Vibrations contactor closed 5 Gn, 5300 Hz Vibrations contactor open 2 Gn, 5300 Hz Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 6 Gn for 11 ms	
206 mm	
213 mm	
219 mm	
9.5 kg	

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0843 - Schneider Electric declaration of conformity
	Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold
	Reference not containing SVHC above the threshold
Product environmental profile	Available
	Product environmental
Product end of life instructions	Available
	₫End of life manual

Contractual warranty

Warranty period

18 months