

Share:



**AP9626**



Be the first to [write a review](#)

Share this Product:

Description: The Step-Down Transformer converts high voltage (208 or 200 VAC) output into low voltage (120 or 100 VAC) output for powering low voltage AC equipment.  
Includes : Rack Mounting Brackets , User Manual



- Product Overview
- Technical Specifications**
- Documentation
- Options
- Ratings & Reviews

**Output**

Print Technical Specification

Nominal Output Voltage	120V
Always on Outlets	12
Maximum Total Current Draw	24

Output Connections  
(12) NEMA 5-20R (Battery Backup)

**Input**

Nominal Input Voltage	208V
Input Connections	NEMA L6-30P
Acceptable Input Voltage	208VAC
Number of Power Cords	1
Load Capacity	5000VA
Maximum Input Current	30A
Maximum Line Current	24A

**Physical**

Maximum Height	3.5inches ( 89mm , 8.9CM )
Maximum Width	17.5inches ( 445mm , 44.5CM )
Maximum Depth	24.0inches ( 610mm , 61.0CM )
Rack Height	2U
Net Weight	95.0lbs. ( 43.18KG )
Shipping weight	110.0lbs. ( 50.0KG )
Shipping Height	10.0inches ( 254mm , 25.4CM )
Shipping Width	24.5inches ( 622mm , 62.2CM )
Shipping Depth	37.5inches ( 953mm , 95.3CM )
Color	Black

**Environmental**

Operating Temperature	32 - 104 °F ( 0 - 40 °C )
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000ft ( 0-3000meters )
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000ft ( 0-15000meters )

**Conformance**

Approvals	CSA, OSHPD, UL 1778
Standard warranty	2 years repair or replace

**Sustainable Offer Status**

PEP	Available in Documentation tab
-----	--------------------------------

WHO WE ARE

[APC History](#)  
[Investor Relations](#)  
[Careers](#)  
[Sustainability](#)

CONNECT WITH US

[Press](#)  
[APC Blog](#)  
[Schneider Electric TV](#)  
[Schneider Electric Data Center Blog](#)  
[Contact Us](#)  
[Rate this website](#)

FIND A RESELLER

CATALOG KEYCODE

[TERMS & CONDITIONS](#) | [PRIVACY STATEMENT](#)

© 2018, APC by Schneider Electric

