





**Amphenol Aerospace**  
 40-60 Delaware Avenue  
 Sidney, NY 13838-1395  
**Phone:** 800-678-0141 - **Fax:** 607-563-5157  
**Email:** info@amphenol-aerospace.com  
**Website:** www.amphenol-aerospace.com

**Joe Ryder**  
 Product Line Manager  
 Core Products  
**Phone:** 607-563-5001  
**Email:** jryder@amphenol-ao.com

## Specifications

|                             |                               |
|-----------------------------|-------------------------------|
| Connector Type              | D38999/                       |
| Shell Style                 | Jam Nut Receptacle            |
| Shell Material              | Aluminum                      |
| Shell Finish                | Electroless Nickel            |
| Insulation Resistance       | 5000 megohms min. @500 VDC25C |
| Operating Temperature [Min] | -65°C                         |
| Operating Temperature [Max] | +200°C                        |
| Shielding Effectiveness     | 65dB@10GHz                    |
| Durability                  | 48 Hour Salt Spray            |
| Contact Type                | A                             |
| Contact Description         | Less Pins                     |

## Contacts

|                                |                         |
|--------------------------------|-------------------------|
| Insert Arrangement             |                         |
| Front Face of Pin Insert Shown |                         |
| Shell Size                     | J                       |
| Insert Arrg                    | 7                       |
| Service Rating                 | Twinax                  |
| Total # Contacts               | 99                      |
| Test Current                   | (22D)5 AMPS, (8)46 AMPS |
| Wire Size for 22D              | 28, 26, 24, 22          |
| Contact Size 22D               | 97                      |
| Number of Contacts             |                         |
| Contact Size 8 Coax            | 2                       |
| Number of Contacts:            |                         |