


13 96 200 T

Pliers for Electrical Installation with tether attachment point



- Multifunctional pliers for the electrical installation; to grip flat and round material, for bending, deburring, cutting cable, stripping and crimping end sleeves (ferrules)
- 6 functions in one pair of pliers
- Smooth surfaces near the tips grip single cores without damaging them; serrated gripping surfaces and pipe grip for gripping flat and round material
- Clear-cut outside edge on the jaw for working on flush-mounted junction boxes and deburring feed-through holes
- Stripping holes for conductors of 0.75 - 1.5 mm² and 2.5 mm²
- Crimp die for wire-end ferrules 0.5 - 2.5 mm²
- Cable shears with (induction-hardened) precision cutting edges for copper and aluminium cables up to 5 x 2.5 mm² / dia. 15 mm
- Gripping, without opening the pliers completely (intelligent latching mechanism in the spring assisted version). The cutting edge remains closed and protected
- Slim dimensions for easy access
- Bolted joint: precise, zero backlash operation of pliers
- High-grade special tool steel, forged, multi stage oil-hardened
- Pliers with integrated, insulated tether attachment point for a tool tether

| | |
|---|------------------------|
| Article No. | 13 96 200 T |
| EAN | 4003773081425 |
| Pliers | chrome plated |
| Head | |
| Handles | |
| Insulation standard | IEC 60900 DIN EN 60900 |
| Cutting capacity copper cable, multiple-stranded mm² | 50 |
| Cutting capacity copper cable, multiple-stranded (diameter) Ø mm | 15 |
| Stripping capacity for cross-sections mm² | 0,75 - 1,5 + 2,5 |
| Capacity in square millimetres mm² | 0,5 - 2,5 |
| AWG | 1/0 |
| Length mm | 200 |
| Net weight g | 277 |



technical change and errors excepted