



- † Red band indicates fully mated
- †† Blue band indicates rear release contact retention system
- ★ .059 dia min.
1.5 dia min., 3 lockwire holes formed lockwire hole design (6 holes) is optional

Note: -Drawing not to Scale
-Dimensions subject to change
-Dimensions are in Inches, Millimeters (MM) & Blue color
Property of Amphenol Aerospace.
All rights reserved.

Part No.:
D38999/24WJ24AN

Amphenol
Aerospace

40-60 Delaware Avenue
Sidney, NY 13838-1395
800-678-0141
Cage Code: 77820
www.amphenol-aerospace.com



Amphenol Aerospace
 40-60 Delaware Avenue
 Sidney, NY 13838-1395
Phone: 800-678-0141 - **Fax:** 607-563-5157
Email: info@amphenol-aerospace.com
Website: www.amphenol-aerospace.com

Joe Ryder
 Product Line Manager
 Core Products
Phone: 607-563-5001
Email: jryder@amphenol-ao.com

Specifications

Connector Type	D38999/
Shell Style	Jam Nut Receptacle
Shell Material	Aluminum
Shell Finish	Olive Drab Cadmium
Insulation Resistance	5000 megohms min. @500 VDC25C
Operating Temperature [Min]	-65°C
Operating Temperature [Max]	+175°C
Shielding Effectiveness	50dB@10GHz
Durability	500 Hour Salt Spray
Contact Type	A
Contact Description	Less Pins

Contacts

Insert Arrangement	
Front Face of Pin Insert Shown	
Shell Size	J
Insert Arrg	24
Service Rating	I
Total # Contacts	24
Test Current	(16)13 AMPS, (12)23 AMPS
Wire Size for 12	14, 12
Contact Size16	12
Number of Contacts	
Contact Size 12	12
Number of Contacts	