



Part Number: 9951

Audio/Control/Communication/Instrumentation, (1) 16 AWG (19x29) TC, PVC-NYL/PVC, TC Braid Shld

Product Description

One 16 AWG stranded (19x29) tinned copper conductors, PVC-Nylon insulation, tinned copper braid shield (90% coverage), PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
16	19x29	TC - Tinned Copper	1

Conductor Count:	1
AWG Size:	16

Insulation

Layer	Material	Nominal Wall Thickness
1	PVC - Polyvinyl Chloride	0.012 in
2	Nylon	0.004 in

Color Chart

Color
White

Outer Shield Material

Type	Material	Coverage [%]
Braid	TC - Tinned Copper	90 %

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.143 in	0.016 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
5.8 Ohm/1000ft	4.3 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
138 pF/ft

Current

Max. Recommended Current [A]
6.5 Amps per conductor @ 25°C

Voltage

Non-UL Voltage Rating
600 V RMS

Electrical Characteristics Notes:	500 megohms/1000 ft. @ 500 VDC
-----------------------------------	--------------------------------

Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-20°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	20 lbs/1000ft
Max Recommended Pulling Tension:	30.4 lbs
Min Bend Radius/Minor Axis:	1.5 in

Standards

Military Specification:	MIL-W-16878E/17 (insulated conductor)
Other Specification:	NEMA HP3

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
------------------	------

Part Number

Plenum (Y/N):	No
---------------	----

Variants

Item #	Color
9951 0091000	WHITE

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.