

**W-Series
WSI 25/1 CC/LED**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com



Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WSI 25/1 CC/LED
Order No.	1966070000
Version	W-Series, Fuse terminal, Rated cross-section: 25 mm ² , Screw connection
GTIN (EAN)	4032248658121
Qty.	12 pc(s).

W-Series
WSI 25/1 CC/LED

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	18 mm	Width (inches)	0.709 inch
Height	81 mm	Height (inches)	3.189 inch
Depth	58 mm	Depth (inches)	2.283 inch
Weight	67 g	Net weight	52.83 g

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	PA 66/6	Colour	Dark Beige
UL 94 flammability rating	V-0		

System specifications

Version	Screw connection, Fuse cartridge, with LED, closed	End cover plate required	Yes
Number of potentials	1	Number of levels	1
No. of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Mounting rail	TS 35	N-function	No
PE function	No	PEN function	No

Additional technical data

Open sides	closed	Type of mounting	Snap-on
------------	--------	------------------	---------

CSA rating data

Certificate No. (CSA)	238018-1868186	Wire cross section max. (CSA)	3 AWG
Wire cross section min. (CSA)	18 AWG		

W-Series
WSI 25/1 CC/LED

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data
Conductors for clamping (rated connection)

Clamping range, rated connection, max.	25 mm ²	Clamping range, rated connection, min.	1.5 mm ²
Connection direction	on side	Cross-section for connected conductor, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, min.	1.5 mm ²
Number of connections	2	Stripping length	11 mm
Tightening torque, max.	2.5 Nm	Tightening torque, min.	2 Nm
Type of connection	Screw connection	Wire connection cross section AWG, max.	AWG 4
Wire connection cross section AWG, min.	AWG 18	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	25 mm ²
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	1.5 mm ²	Wire connection cross section, finely stranded, max.	25 mm ²
Wire connection cross section, solid core max. rated connection	25 mm ²	Wire connection cross section, solid core, min. rated connection	1.5 mm ²
Wire connection cross section, stranded, rated connection, max.	25 mm ²	Wire connection cross section, stranded, rated connection, min.	1.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, max.	25 mm ²	Wire connection cross-section, finely stranded, min.	1.5 mm ²

Dimensions

TS 35 offset	40.5 mm
--------------	---------

Fuse terminals

Cartridge fuse	max. 3W for gG/gL max. 1.2W for aM	Fuse holder (cartridge holder)	Pivoting
Permitted power loss for fuse with semiconductor protection		Power loss, 1-pole ; 2-pole ; 3-pole	

Rating data

Rated cross-section	25 mm ²	Rated voltage	690 V
Rated voltage to adjoining terminal	690 V	Rated current	32 A
Current at maximum wires	32 A	Standards	IEC 60947-7-3
Volume resistance according to IEC 60947-7-x	0.32 mΩ	Rated impulse withstand voltage	6 kV
Pollution severity	3		

Classifications

ETIM 3.0	EC000899	ETIM 4.0	EC000899
ETIM 5.0	EC000899	ETIM 6.0	EC000899
UNSPSC	30-21-18-01	eClass 6.2	27-14-11-16
eClass 7.1	27-14-11-16	eClass 8.1	27-14-11-16
eClass 9.0	27-14-11-16	eClass 9.1	27-14-11-16

Product information

Descriptive text technical data	Suitable for fuse cartridges in accordance with IEC 60269-6 with power losses up to max. 3 W. Suitable for fuse cartridges in accordance with UL 248-4.
---------------------------------	---

Creation date September 19, 2017 10:26:47 PM CEST

Data sheet**W-Series
WSI 25/1 CC/LED**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue

[CAT 1 TERM 16/17 EN](#)

Engineering Data

[EPLAN, WSCAD, Zuken E3.S](#)

Data sheet

W-Series
WSI 25/1 CC/LED

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

Drawings

