### **Encapsulation Resins**

## Technical Data Sheet



# **UR5641**Optically Clear Flame Retardant Polyurethane Resin

UR5641 is a two-part, semi-rigid optically clear flame retardant polyurethane resin ideal for use in protective applications. Due to a carefully selected blend of components an extremely durable, low viscosity system is achieved which can be used for a wide variety of applications.

- Water white transparency; ideal for LED applications
- Flame retardant resin; achieves UL94 V-0 as a clear resin system
- Excellent resistance to yellowing; good resistance to UV light
- Good resistance to weather, acids and alkalis, water and mould growth; suitable for a range of environments

Approvals RoHS-2 Compliant (2015/863/EU): Yes

UL Approval: Meets UL94 V-0

#### **Typical Properties**

Liquid Properties: Base Material Polyurethane

Density Part A - Resin (g/ml) 1.14 Density Part B - Hardener (g/ml) 1.13 Part A Viscosity (mPa s @ 23°C) 250 Part B Viscosity (mPa s @ 23°C) 4500 Mixed System Viscosity (mPa s @ 23°C) 900 Mix Ratio (Weight) 0.75:1 Mix Ratio (Volume) 0.75:1 Usable Life (20°C) 12 mins Gel Time (23°C) 25 mins Cure Time (23 °C) 24 hours Cure Time (60 °C) 4 hours Colour Part A - Resin Clear Colour Part B - Hardener

Storage Conditions Dry Conditions: Above 15°C, Below 35°C

<1%

Shelf Life 12 months Exotherm (Measured on a 100ml sample in a cylinder of diameter 49.4mm @ 23°C) <70°C

#### Copyright Electrolube 2013

Shrinkage

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification.

Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.

Ashby Park, Coalfield Way, Ashby de la Zouch, Leicestershire LE65 1JR T +44 (0)1530 419 600 F +44 (0)1530 416 640 BS EN ISO 9001:2008 Certificate No. FM 32082





Cured System: Thermal Conductivity (W/m.K) 0.30
Cured Density (g/ml) 1.13

Temperature Range (°C) -40 to +120

Max Temperature Range (Short Term (°C)/30mins)
(Application and Geometry Dependent)

Dielectric Strength (kV/mm)

Volume Resistivity (ohm-cm)

Shore Hardness @ 25°C

+130

+130

11

A60

Colour (Mixed System)

Refractive Index

A00

Colourless

1.485

Flame Retardancy Meets UL94 V-0
Comparative Tracking Index Not Measured

Water Absorption (9.7mm thick disk, 51mm diameter) 2.0%/ 2.3%


10 days @ 20°C/1 hour @ 100°C

Elongation at Break 80% Tensile Modulus (MPa) 1.7

#### **Mixing Procedures**


#### **Resin Packs**


When in Resin pack form, the resin and hardener are mixed by removing the clip and moving the contents around inside the pack until thoroughly mixed. To remove the clip, remove both end caps, grip each end of the pack and pull apart gently. By using the removed clip, take special care to push unmixed material from the corners of the pack. Mixing normally takes from two to four minutes depending on the skill of the operator and the size of the pack. Both the resin and hardener are evacuated prior to packing so the system is ready for use immediately after mixing. The corner may be cut from the pack so that it may be used as a simple dispenser.














#### Copyright Electrolube 2013

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification.

Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.

Ashby Park, Coalfield Way, Ashby de la Zouch, Leicestershire LE65 1JR T +44 (0)1530 419 600 F +44 (0)1530 416 640 BS EN ISO 9001:2008 Certificate No. FM 32082





#### **Bulk Mixing**

When mixing, care must be taken to avoid the introduction of excessive amounts of air. Automatic mixing equipment is available which will not only mix both the resin and hardener accurately in the correct ratio but do this without introducing air. Containers of Part A (Resin) and Part B (Hardener) should be kept sealed at all times when not in use to prevent the ingress of moisture. Bulk material must be thoroughly mixed before use. Incomplete mixing will result in erratic or partial curing.

#### **Additional Information**

Cleaning: It is far easier for machines & containers to be cleaned before the resin has been allowed

to cure. Electrolube's RRS is suitable for cleaning machines and containers and cured

resin may be slowly softened and removed by soaking in our RRS.

**Curing:** Do not heat cure large volumes immediately. Allow these to gel at room temperature and

post-cure at high temperature if required (refer to liquid properties for details). Small volumes (250ml) may be heat cured immediately. It is recommended to heat cure very

small volumes (<50ml) at 40°C.

Storage: When storing under very cold conditions, the hardener may crystallise. If this occurs,

simply warm (40°C) the container gently until all crystals have re-melted.

Health & Safety: Always refer to the Health & Safety data sheet before use. These can be downloaded

from www.electrolube.com

Revision 2: March 2018