

78 61 140 ESD

Electronic *Super Knips*® XL ESD



- For ultra fine cutting work, e.g. in electronics and fine mechanics
- Ground, very sharp cutting edges without bevel
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Precision shaped tips cut wires resting on a board from 0.2 mm dia.
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter
- Cutting-edge hardness approx. 64 HRC
- Cutting edges additionally induction hardened
- Special tool steel, oil hardened in multiple stages

ESD pliers (electrostatic discharge)




electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

Article No.	78 61 140 ESD
EAN	4003773081708
Pliers	burnished
Head	
Handles	with multi-component grips
Cutting capacities medium hard wire (diameter) Ø mm	1,4
Cutting capacities soft wire (diameter) Ø mm	0,2 - 2,1
B mm	12,3
D mm	9,2
A mm	15,7
Length mm	140
Net weight g	77



technical change and errors excepted