

Safety Data Sheet

According to Annex II to REACH - Regulation 2015/830

SECTION 1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name **AS1700**

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use **Adhesive sealant.**

1.3. Details of the supplier of the safety data sheet

Name **ACC Silicones LTD**
Full address **Amber House Showground Road**
District and Country **TA6 6A Bridgwater (Somerset)**
England
Tel. **+44(0)1278411400**
Fax **+44(0)1278411444**

e-mail address of the competent person responsible for the Safety Data Sheet **sean.stoodley@acc-silicones.com**

1.4. Emergency telephone number

For urgent inquiries refer to **For all enquiries except Sweden: +44(0)1278411400**

Sweden: Ring 112 vid inträffade förgiftningstillbud och begär giftinformation - dygnet runt.
Ring 010-456-6700 i mindre brådskande fall - dygnet runt. Allmänna och förebyggande frågor om akuta förgiftningar besvaras vardagar kl 9-17.

SECTION 2. Hazards identification

2.1. Classification of the substance or mixture

The product is not classified as hazardous pursuant to the provisions set forth in EC Regulation 1272/2008 (CLP). However, since the product contains hazardous substances in concentrations such as to be declared in section no. 3, it requires a safety data sheet with appropriate information, compliant to (EU) Regulation 2015/830.

Hazard classification and indication: --

2.2. Label elements

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.

Hazard pictograms: --

Signal words: --

Hazard statements:
EUH210 Safety data sheet available on request.

Precautionary statements: --

2.3. Other hazards

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

SECTION 3. Composition/information on ingredients

3.1. Substances

Information not relevant

3.2. Mixtures

Contains:

Identification	x = Conc. %	Classification 1272/2008 (CLP)
AMORPHOUS SILICATE HYDRATE		
CAS	7631-86-9 10 ≤ x < 30	Substance with a community workplace exposure limit.
EC	231-545-4	
INDEX		
Reg. no.	01-2119379499-16-0134	
TETRA-ISOPROPYLTITANATE		
CAS	546-68-9 1 ≤ x < 5	Flam. Liq. 3 H226, Eye Irrit. 2 H319, STOT SE 3 H336
EC	208-909-6	
INDEX		
Reg. no.	01-2119967389-17	
VINYLTRIMETHOXYSILANE		
CAS	2768-02-7 1 ≤ x < 5	Flam. Liq. 3 H226, Acute Tox. 4 H332, STOT RE 2 H373
EC	220-449-8	
INDEX		
Reg. no.	01-2119513215-52	

The full wording of hazard (H) phrases is given in section 16 of the sheet.

SECTION 4. First aid measures

4.1. Description of first aid measures

EYES: Remove contact lenses, if present. Wash immediately with plenty of water for at least 15 minutes, opening the eyelids fully. If problem persists, seek medical advice.

SKIN: Remove contaminated clothing. Wash immediately with plenty of water. If irritation persists, get medical advice/attention. Wash contaminated clothing before using it again.

INHALATION: Remove to open air. In the event of breathing difficulties, get medical advice/attention immediately.

INGESTION: Get medical advice/attention. Induce vomiting only if indicated by the doctor. Never give anything by mouth to an unconscious person, unless authorised by a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Specific information on symptoms and effects caused by the product are unknown.

4.3. Indication of any immediate medical attention and special treatment needed

Information not available

SECTION 5. Firefighting measures

5.1. Extinguishing media

SUITABLE EXTINGUISHING EQUIPMENT

Extinguishing substances are: carbon dioxide, foam, chemical powder. For product loss or leakage that has not caught fire, water spray can be used to disperse flammable vapours and protect those trying to stem the leak.

UNSUITABLE EXTINGUISHING EQUIPMENT

Do not use jets of water. Water is not effective for putting out fires but can be used to cool containers exposed to flames to prevent explosions.

5.2. Special hazards arising from the substance or mixture

HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE

SECTION 5. Firefighting measures ... / >>

Excess pressure may form in containers exposed to fire at a risk of explosion. Do not breathe combustion products.

5.3. Advice for firefighters

GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

SECTION 6. Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Block the leakage if there is no hazard.

Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

6.2. Environmental precautions

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

6.3. Methods and material for containment and cleaning up

Collect the leaked product into a suitable container. If the product is flammable, use explosion-proof equipment. Evaluate the compatibility of the container to be used, by checking section 10. Absorb the remainder with inert absorbent material.

Make sure the leakage site is well aired. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

6.4. Reference to other sections

Any information on personal protection and disposal is given in sections 8 and 13.

SECTION 7. Handling and storage

7.1. Precautions for safe handling

Keep away from heat, sparks and naked flames; do not smoke or use matches or lighters. Without adequate ventilation, vapours may accumulate at ground level and, if ignited, catch fire even at a distance, with the danger of backfire. Avoid bunching of electrostatic charges. Do not eat, drink or smoke during use. Remove any contaminated clothes and personal protective equipment before entering places in which people eat. Avoid leakage of the product into the environment.

7.2. Conditions for safe storage, including any incompatibilities

Store only in the original container. Store in a well ventilated place, keep far away from sources of heat, naked flames and sparks and other sources of ignition. Keep containers away from any incompatible materials, see section 10 for details.

7.3. Specific end use(s)

Information not available

SECTION 8. Exposure controls/personal protection

8.1. Control parameters

Regulatory References:

DEU	Deutschland	TRGS 900 (Fassung 31.1.2018 ber.) - Liste der Arbeitsplatzgrenzwerte und Kurzzeitwerte
GBR	United Kingdom	EH40/2005 Workplace exposure limits
EU	OEL EU	Directive (EU) 2017/2398; Directive (EU) 2017/164; Directive 2009/161/EU; Directive 2006/15/EC; Directive 2004/37/EC; Directive 2000/39/EC; Directive 91/322/EEC.

SECTION 8. Exposure controls/personal protection ... / >>

AMORPHOUS SILICATE HYDRATE

Threshold Limit Value

Type	Country	TWA/8h		STEL/15min		
		mg/m ³	ppm	mg/m ³	ppm	
AGW	DEU	4				INHAL
MAK	DEU	4				INHAL
WEL	GBR	6				INHAL
WEL	GBR	2.4				RESP
OEL	EU	6				INHAL
OEL	EU	2.4				RESP

Health - Derived no-effect level - DNEL / DMEL

Route of exposure	Effects on consumers				Effects on workers			
	Acute	Acute	Chronic	Chronic	Acute	Acute	Chronic	Chronic
	local	systemic	local	systemic	local	systemic	local	systemic
Inhalation					4 mg/m ³	VND	4 mg/m ³	VND

VINYLTRIMETHOXYSILANE

Predicted no-effect concentration - PNEC

Normal value in fresh water	0.34	mg/l
Normal value in marine water	0.034	mg/l
Normal value for water, intermittent release	3.4	mg/l
Normal value of STP microorganisms	110	mg/l
Normal value for the terrestrial compartment	0.046	mg/kg

Health - Derived no-effect level - DNEL / DMEL

Route of exposure	Effects on consumers				Effects on workers			
	Acute	Acute	Chronic	Chronic	Acute	Acute	Chronic	Chronic
	local	systemic	local	systemic	local	systemic	local	systemic
Inhalation					VND	4.9 mg/m ³	VND	4.9 mg/m ³
Skin					VND	0.69 mg/kg bw/d	VND	0.69 mg/kg bw/d

Legend:

(C) = CEILING ; INHAL = Inhalable Fraction ; RESP = Respirable Fraction ; THORA = Thoracic Fraction.
 VND = hazard identified but no DNEL/PNEC available ; NEA = no exposure expected ; NPI = no hazard identified.

8.2. Exposure controls

As the use of adequate technical equipment must always take priority over personal protective equipment, make sure that the workplace is well aired through effective local aspiration.

When choosing personal protective equipment, ask your chemical substance supplier for advice.

Personal protective equipment must be CE marked, showing that it complies with applicable standards.

HAND PROTECTION

Protect hands with category III work gloves (see standard EN 374).

The following should be considered when choosing work glove material: compatibility, degradation, failure time and permeability.

The work gloves' resistance to chemical agents should be checked before use, as it can be unpredictable. The gloves' wear time depends on the duration and type of use.

SKIN PROTECTION

Wear category I professional long-sleeved overalls and safety footwear (see Directive 89/686/EEC and standard EN ISO 20344). Wash body with soap and water after removing protective clothing.

EYE PROTECTION

Wear airtight protective goggles (see standard EN 166).

RESPIRATORY PROTECTION

If the threshold value (e.g. TLV-TWA) is exceeded for the substance or one of the substances present in the product, use a mask with a type B filter whose class (1, 2 or 3) must be chosen according to the limit of use concentration. (see standard EN 14387). In the presence of gases or vapours of various kinds and/or gases or vapours containing particulate (aerosol sprays, fumes, mists, etc.) combined filters are required.

Respiratory protection devices must be used if the technical measures adopted are not suitable for restricting the worker's exposure to the threshold values considered. The protection provided by masks is in any case limited.

If the substance considered is odourless or its olfactory threshold is higher than the corresponding TLV-TWA and in the case of an emergency, wear open-circuit compressed air breathing apparatus (in compliance with standard EN 137) or external air-intake breathing apparatus (in compliance with standard EN 138). For a correct choice of respiratory protection device, see standard EN 529.

ENVIRONMENTAL EXPOSURE CONTROLS

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

SECTION 9. Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	paste
Colour	colourless
Odour	characteristic
Odour threshold	Not available
pH	Not available
Melting point / freezing point	Not available
Initial boiling point	Not available
Boiling range	Not available
Flash point	> 150 °C
Evaporation Rate	Not available
Flammability of solids and gases	Not available
Lower inflammability limit	Not available
Upper inflammability limit	Not available
Lower explosive limit	Not available
Upper explosive limit	Not available
Vapour pressure	Not available
Vapour density	Not available
Relative density	Not available
Solubility	immiscible with water
Partition coefficient: n-octanol/water	Not available
Auto-ignition temperature	> 400 °C
Decomposition temperature	Not available
Viscosity	Not available
Explosive properties	Not available
Oxidising properties	Not available

9.2. Other information

Information not available

SECTION 10. Stability and reactivity

10.1. Reactivity

There are no particular risks of reaction with other substances in normal conditions of use.

10.2. Chemical stability

The product is stable in normal conditions of use and storage.

10.3. Possibility of hazardous reactions

The vapours may also form explosive mixtures with the air.

10.4. Conditions to avoid

Avoid overheating. Avoid bunching of electrostatic charges. Avoid all sources of ignition.

10.5. Incompatible materials

Information not available

10.6. Hazardous decomposition products

In the event of thermal decomposition or fire, gases and vapours that are potentially dangerous to health may be released.

SECTION 11. Toxicological information

In the absence of experimental data for the product itself, health hazards are evaluated according to the properties of the substances it contains, using the criteria specified in the applicable regulation for classification.

It is therefore necessary to take into account the concentration of the individual hazardous substances indicated in section 3, to evaluate the

SECTION 11. Toxicological information ... / >>

toxicological effects of exposure to the product.

11.1. Information on toxicological effects

Metabolism, toxicokinetics, mechanism of action and other information

Information not available

Information on likely routes of exposure

Information not available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Information not available

Interactive effects

Information not available

ACUTE TOXICITY

LC50 (Inhalation) of the mixture:	> 20 mg/l
LD50 (Oral) of the mixture:	Not classified (no significant component)
LD50 (Dermal) of the mixture:	Not classified (no significant component)

VINYLTRIMETHOXYSILANE

LD50 (Oral)	7430 mg/kg (Rat)
LD50 (Dermal)	3460 mg/kg (Rabbit)
LC50 (Inhalation)	16.79 mg/l/4h (Rat)

AMORPHOUS SILICATE HYDRATE

LD50 (Oral)	> 2000 mg/kg Rat
LD50 (Dermal)	> 2000 mg/kg Rat
LC50 (Inhalation)	> 2.2 mg/l/1h Rat

SKIN CORROSION / IRRITATION

Does not meet the classification criteria for this hazard class

SERIOUS EYE DAMAGE / IRRITATION

Does not meet the classification criteria for this hazard class

RESPIRATORY OR SKIN SENSITISATION

Does not meet the classification criteria for this hazard class

GERM CELL MUTAGENICITY

Does not meet the classification criteria for this hazard class

CARCINOGENICITY

Does not meet the classification criteria for this hazard class

REPRODUCTIVE TOXICITY

Does not meet the classification criteria for this hazard class

STOT - SINGLE EXPOSURE

Does not meet the classification criteria for this hazard class

STOT - REPEATED EXPOSURE

Does not meet the classification criteria for this hazard class

SECTION 11. Toxicological information ... / >>

ASPIRATION HAZARD

Does not meet the classification criteria for this hazard class

SECTION 12. Ecological information

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

12.1. Toxicity

VINYLTRIMETHOXYSILANE
LC50 - for Fish 100 mg/l/96h

12.2. Persistence and degradability

AMORPHOUS SILICATE HYDRATE
Solubility in water 0,1 - 100 mg/l
Degradability: information not available

12.3. Bioaccumulative potential

AMORPHOUS SILICATE HYDRATE
Partition coefficient: n-octanol/water 0.53

12.4. Mobility in soil

Information not available

12.5. Results of PBT and vPvB assessment

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

12.6. Other adverse effects

Information not available

SECTION 13. Disposal considerations

13.1. Waste treatment methods

Reuse, when possible. Neat product residues should be considered special non-hazardous waste.
Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.
CONTAMINATED PACKAGING
Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

SECTION 14. Transport information

The product is not dangerous under current provisions of the Code of International Carriage of Dangerous Goods by Road (ADR) and by Rail (RID), of the International Maritime Dangerous Goods Code (IMDG), and of the International Air Transport Association (IATA) regulations.

14.1. UN number

Not applicable

14.2. UN proper shipping name

Not applicable

14.3. Transport hazard class(es)

Not applicable

SECTION 14. Transport information ... / >>**14.4. Packing group**

Not applicable

14.5. Environmental hazards

Not applicable

14.6. Special precautions for user

Not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Information not relevant

SECTION 15. Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**Seveso Category - Directive 2012/18/EC: NoneRestrictions relating to the product or contained substances pursuant to Annex XVII to EC Regulation 1907/2006
None

Substances in Candidate List (Art. 59 REACH)

On the basis of available data, the product does not contain any SVHC in percentage greater than 0,1%.

Substances subject to authorisation (Annex XIV REACH)

None

Substances subject to exportation reporting pursuant to (EC) Reg. 649/2012:

None

Substances subject to the Rotterdam Convention:

None

Substances subject to the Stockholm Convention:

None

Healthcare controls

Information not available**15.2. Chemical safety assessment**

No chemical safety assessment has been processed for the mixture and the substances it contains.

SECTION 16. Other information

Text of hazard (H) indications mentioned in section 2-3 of the sheet:

Flam. Liq. 3	Flammable liquid, category 3
Acute Tox. 4	Acute toxicity, category 4
STOT RE 2	Specific target organ toxicity - repeated exposure, category 2
Eye Irrit. 2	Eye irritation, category 2
STOT SE 3	Specific target organ toxicity - single exposure, category 3
H226	Flammable liquid and vapour.
H332	Harmful if inhaled.
H373	May cause damage to organs through prolonged or repeated exposure.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
EUH210	Safety data sheet available on request.

LEGEND:

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- CAS NUMBER: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)

SECTION 16. Other information ... / >>

- CE NUMBER: Identifier in ESIS (European archive of existing substances)- CLP: EC Regulation 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals
- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX NUMBER: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PNEC: Predicted no effect concentration
- REACH: EC Regulation 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).

GENERAL BIBLIOGRAPHY

1. Regulation (EC) 1907/2006 (REACH) of the European Parliament
2. Regulation (EC) 1272/2008 (CLP) of the European Parliament
3. Regulation (EU) 790/2009 (I Atp. CLP) of the European Parliament
4. Regulation (EU) 2015/830 of the European Parliament
5. Regulation (EU) 286/2011 (II Atp. CLP) of the European Parliament
6. Regulation (EU) 618/2012 (III Atp. CLP) of the European Parliament
7. Regulation (EU) 487/2013 (IV Atp. CLP) of the European Parliament
8. Regulation (EU) 944/2013 (V Atp. CLP) of the European Parliament
9. Regulation (EU) 605/2014 (VI Atp. CLP) of the European Parliament
10. Regulation (EU) 2015/1221 (VII Atp. CLP) of the European Parliament
11. Regulation (EU) 2016/918 (VIII Atp. CLP) of the European Parliament
12. Regulation (EU) 2016/1179 (IX Atp. CLP)
13. Regulation (EU) 2017/776 (X Atp. CLP)

- The Merck Index. - 10th Edition
- Handling Chemical Safety
- INRS - Fiche Toxicologique (toxicological sheet)
- Patty - Industrial Hygiene and Toxicology
- N.I. Sax - Dangerous properties of Industrial Materials-7, 1989 Edition
- IFA GESTIS website
- ECHA website
- Database of SDS models for chemicals - Ministry of Health and ISS (Istituto Superiore di Sanità) - Italy

Note for users:

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.

Changes to previous review:

The following sections were modified:

01 / 02 / 03 / 04 / 08 / 11 / 12 / 14 / 15.