

# **UNITRONIC® BUS ASI**

Communication at sensor/actuator level. Halogen free (rubber), UL-approval, oil resistant (TPE). Temperature range from -40°C bis +90°C

### Info

"LD" = Long Distance

LAPP KABEL STUTTGART UNITRONIC® BUS ASI

*LAPP KABEL* STUतिGART UNITRONIC® BUS ASI

LAPP KABEL STUTTGART UNITRONIC BUS ASI







Temperature-resistant



Halogen-free



Good chemical resistance



Mechanical and plant engineering



Automation & amp; fältinstallation

### **Benefits**

The new BUS ASI LD 2 x 2.5 (Long Distance) allows even modules located further away to be connected. AS-I power supplies can be reduced. The BUS ASI LD is downwards-compatible with version 1.5. The rubber versions are halogen-free

## **Application range**

Communication at sensor/actuator level

Sensor-/actuator wiring

For fixed installation as well as occasional flexing at free, non-continuously recurring movement without tensile load. The TPE version has an oil-resistant outer sheath. It is suitable for wet areas, in particular in conjunction with water-soluble cooling lubricants.

Last Update (01.11.2017)
©2017 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02\_03.16



# **UNITRONIC® BUS ASI**

### **Product features**

Data and power are transmitted via an unscreened, geometrically coded two-core flat cable (protection against polarity reversal).

The conductor is contacted by "piercing technology" within the ASI modules.

The sensors are connected to the ASI modules (coupling modules) using round cables (connection cables).

### Norm references / Approvals

ASI is standardised Europe-wide in EN 50295 and internationally in IEC 62026-2.

PVC version with UL/CSA (CMX) certification

UL/CSA version: CMG c(UL)us or (UL)CL2 or AWM 300V FT4 certified

### **Product Make-up**

Extra-fine wire, tinned copper strands Core insulation: blue and brown

Outer sheath:

rubber (G), halogenfree

thermoplastic elastomers (TPE)

PVC

Outer sheath: yellow (RAL 1023), black (RAL 9005), red (RAL 3000)

Colour: red (RAL 3000)

### **Technical Data**

Classification: ETIM 5.0 Class-ID: EC000830

ETIM 5.0 Class-Description: Data cable

Peak operating voltage: Yellow: 300 V (not for power applications)

Black: 300 V (not for power applications)

Red: 300 V

Conductor resistance: 1.5 mm<sup>2</sup>: max. 13.7 Ohm/km

2.5 mm2: max. 8.21 Ohm/km

Minimum bending radius: Fixed installation: 12 mm

Flexible use 24 mm

Test voltage: Core/core: 2000 V

Temperature range: Dependent on outer sheath material:

PVC: -30°C to +90°C

Other materials: -40°C to +85°C

During installation: PVC -20 °C to +90 °C Other materials: -30 °C to +85 °C

### **Note**

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Lapp Kabel is a member of the AS-International Association

Photographs are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

# **UNITRONIC® BUS AS**

### Article number Article designation Outer sheath material Outer sheath colour Application Number of cores and Copper index (kg/km) Weight (kg/km) mm<sup>2</sup> per conductor For fixed and flexible applications (19-wire stranded conductor) 29 85 2170228 UNITRONIC® BUS EPDM (rubber) vellow Data and power 2 x 1.5 ASI (G) transmission 2170229 UNITRONIC® BUS Transmission of 30 V 2 x 1.5 29 85 EPDM (rubber) black DC auxiliary power ASI (G) UNITRONIC® BUS 48 85 2170371 EPDM (rubber) yellow Data and power 2 x 2.5 ASI LD (G) transmission 2170372 UNITRONIC® BUS EPDM (rubber) black Transmission of 30 V 2 x 2.5 48 85 ASI LD (G) DC auxiliary power 2170230 UNITRONIC® BUS TPE yellow Data and power 2 x 1.5 29 64 ASI (TPE) transmission TPE Transmission of 30 V 2 x 1.5 29 64 2170231 UNITRONIC® BUS black ASI (TPE) DC auxiliary power 2170232 UNITRONIC® BUS TPE Transmission of 230 2 x 1.5 29 64 red ASI (TPE) V AC auxiliary power PVC UL/CSA (CMG) 2 x 1.5 29 70 2170842 UNITRONIC® BUS vellow Data and power ASI (PVC) A transmission 29 70 Transmission of 30 V 2 x 1.5 2170843 UNITRONIC® BUS PVC UL/CSA (CMG) black ASI (PVC) A DC auxiliary power 2170844 UNITRONIC® BUS PVC UL/CSA (CMG) red Transmission of 230 2 x 1.5 29 70 ASI (PVC) A V AC auxiliary power



# **UNITRONIC® BUS ASI**

