

KEMET Part Number: C1812C560KHGACTU
(C1812C560KHGAC7800)

SMD Comm COG HV, Ceramic, 56 pF, 10%, 3,000 V, COG, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 1812



Dimensions

| | |
|----------|-----------------|
| L | 4.5mm +/-0.3mm |
| W | 3.2mm +/-0.3mm |
| T | 1.6mm +/-0.20mm |
| B | 0.6mm +/-0.35mm |

Packaging Specifications

| | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 1000 |

General Information

| | |
|----------------------|--|
| Supplier: | KEMET |
| Series: | SMD Comm COG HV |
| Style: | SMD Chip |
| Description: | SMD, MLCC, Ultra-Stable, Low Loss, Class I |
| Features: | Ultra-Stable, Low Loss, Class I |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Failure Rate: | N/A |
| Chip Size: | 1812 |

Specifications

| | |
|---|---------------------|
| Capacitance: | 56 pF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 3000 VDC |
| Dielectric Withstanding Voltage: | 3,600 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | COG |
| Dissipation Factor: | 0.1% 1MHz 25C |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |