

77 32 115


Electronics Diagonal Cutter



- For fine cutting work, e.g. in electronics and fine mechanics
- Load-optimised for a more direct feel when working
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish (only finish 2) together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 60 HRC
- Narrow sleeves pulled up to the head of the pliers enable the tool to be guided securely and comfortably, also between thumb and index finger
- Ball bearing chrome steel
- Pointed head, with small bevel
- Cutting edge hardness approx. 60 HRC



Article No.	77 32 115
EAN	4003773044307
Head	mirror polished
Handles	with multi-component grips
Style	3
Cutting capacities medium hard wire (diameter) Ø mm	1,0
Cutting capacities hard wire (diameter) Ø mm	0,5
Cutting capacities soft wire (diameter) Ø mm	0,3 - 1,3
D mm	7,0
B mm	13,0
A mm	11,0
Length mm	115
Net weight g	80



technical change and errors excepted

