

TERMINAL LOCATION DIAGRAM

TOL = ± .010

REV. 3 1/20/98

COIL: @ 25°C

RESISTANCE 180-260 OHMS

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 13.0 VDC

MUST RELEASE 10.1 VDC MAX. 2.3 VDC MIN.

ENVIRONMENT:


VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 ± 1 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 15 MS MAX.
CONTACT BOUNCE 5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 30 MICROAMPS
30 MILLIVOLTS DC OR PEAK AC
100,000 OPERATIONS MIN.

DR. OSW 8/10/83 CK. 1/20/98

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. OPL
CUST. NO. M5757/1-026

TYPE 'RD' RELAY

RD6CA2600